

60A – 200A Base & DIN rail mounted UL fuse class J, T

Disconnect
switches
Fusible

For a complete assembly,
please select one of each:

- 1 switch
- 1 handle
- 1 shaft
- 1 terminal lug kit



OS60J12




OXF6X210



OHB65J6




OS60J12



OS100J03



OHB65J6




OXF6X



OXF6X-45



OHB4



OSV250

60 – 200 Amp switches, 600V

UL general purpose amp rating	UL Fuse type 600V	Maximum horsepower rating					Catalog number	List price
		Three phase						
		200V	208V	240V	480V	600V		
2 pole								
200	J	—	—	—	—	—	OS200J02 OS200J11	\$ 1240
3 pole								
60	J	15	15	15	30	50	OS60J12	380
100	J	25	25	30	60	75	OS100J03	520
200	J	50	50	60	125	150	OS200J03	1380
200	J	50	50	60	125	150	OS200J12	1380
4 pole								
60	J	15	15	15	30	50	OS60J22F	490
100	J	25	25	30	60	75	OS100J04F	660
200	J	50	50	60	125	150	OS200J04	1725
200	J	50	50	60	125	150	OS200J13	1725
200	J	50	50	60	125	150	OS200J22	1725

Pistol handles — □ .24 x .24" (□ 6 x 6mm)

UL/NEMA type	IEC type	Color	Length in/mm	Marking	De- featable	Pad- lockable	Weight (lbs.)	Catalog number	List price
1,3R,12	IP65	Black	2.6/65	O/I & Off/On	Yes	Yes	0.29	OHB65J6	\$ 80
1,3R,12	IP65	Red/Yel	2.6/65	O/I & Off/On	Yes	Yes	0.29	OHY65J6	80
1,3R,12	IP65	Black	3.1/80	O/I & Off/On	Yes	Yes	0.30	OHB80J6	90
1,3R,12	IP65	Red/Yel	3.1/80	O/I & Off/On	Yes	Yes	0.30	OHY80J6	90
1,3R,4,4X,12	IP65	Black	3.1/80	O/I & Off/On	Yes	Yes	0.30	OHB80L6	130
1,3R,4,4X,12	IP65	Red/Yel	3.1/80	O/I & Off/On	Yes	Yes	0.30	OHY80L6	130

Shafts — □ .24 x .24" (□ 6 x 6mm)

Shaft length (inches/mm)	Mounting depth (inches)	Weight (lbs.)	Catalog number	List price
5.9/150	5.0 – 8.5	0.09	OXF6X150	\$ 12
8.3/210	7.4 – 11.0	0.13	OXF6X210	16
11.4/290	10.5 – 14.0	0.18	OXF6X290	20
14.2/360	13.3 – 16.8	0.23	OXF6X360	24
16.9/430	16 – 19.7	0.27	OXF6X430	28

Twisted shafts — Rotates handle 45° □ .24 x .24" (□ 6 x 6mm)

Shaft length (inches/mm)	Mounting depth (inches)	Weight (lbs.)	Catalog number	List price
5.1/130	4.3 – 7.8	0.08	OXF6X130-45	\$ 12
8.3/210	7.4 – 11.0	0.13	OXF6X210-45	16
11.4/290	10.5 – 14.0	0.18	OXF6X290-45	20
14.2/360	13.3 – 16.8	0.23	OXF6X360-45	24

Direct mount handle — mounts directly to switch, no shaft necessary

For use on	Color	Marking	Length mm	Padlockable	Weight (lbs.)	Catalog number	List price
OS60 - OS100	Black	O/I	50	Yes	0.10	OHB4	\$ 60
OS200	Black Red/Yel	O/I	—	Yes	0.30	OSV200BK OSVY200BK	130