

Eaton's Arrow Hart
Color coded locking devices

Eaton's Arrow Hart Color Coded Locking Devices

Arrow Hart



Eaton's **color coded locking devices** are an **industry-first solution** that adds six voltage rating color codes to locking plugs, connectors, inlets, outlets and receptacles.

EATON

Powering Business Worldwide

The superior safety of Eaton's Arrow Hart locking devices has been enhanced with **color coding** to provide you a quick, clear and easy way to **identify your circuit voltage**. Designed to provide the long lasting, dependable service you've come to expect from Arrow Hart plugs and connectors, our **color coded locking devices** are the perfect solution for your commercial and industrial applications.

Features & benefits

- Six color codes consistent with IEC 60309 standard to identify voltage ratings at a glance
 - Voltage ratings are printed on device in a location which is visible even when devices are mated
 - Ergonomic ultra grip design on plugs and connectors are easier to handle during use
 - Double dovetail cord grip provides superior cord alignment and clamp force for wire retention
- 

Connect with Color

Find your voltage. Find your NEMA. Find your color.

Use the chart below to **find the color** for your devices. See our NEMA selector guide for our full product offering.

Voltage	NEMA	Color
125 V/AC	L5	
125/250 V/AC	L10, L14, Non-NEMA	
250 V/AC	L6	
3Ø 250 V/AC	L11, L15	
3ØY 120/208 V/AC	L18, L21, Non-NEMA	
277 V/AC	L7	
480 V/AC	L8	
3Ø 480 V/AC	L16	
3ØY 277/480 V/AC	L19, L22	
3Ø 600 V/AC	L17	
3ØY 347/600 V/AC	L20, L23	

Perfect for: *Welding, generators, power distribution units, stage and entertainment equipment, trade shows, conventions, temporary power, industrial machinery and equipment*



Plug



Connector

Arrow Hart color coded ultra grip locking devices

20A Industrial grade locking devices

Pole-Wire	NEMA		V/AC	Color	Plug	Connector	Receptacle	Flanged Inlet	Flanged Outlet
2P-3W	L5-20		125	Yellow & black	AHCL520P	AHCL520C	AHCL520R	AHCL520FI	AHCL520FO
	L6-20		250	Blue & black	AHCL620P	AHCL620C	AHCL620R	AHCL620FI	AHCL620FO
	L7-20		277	Gray & black	AHCL720P	AHCL720C	AHCL720R	AHCL720FI	AHCL720FO
	L8-20		480	Red & black	AHCL820P	AHCL820C	AHCL820R	AHCL820FI	AHCL820FO

Arrow Hart color coded ultra grip locking devices

20A Industrial grade locking devices



Plug



Connector



Receptacle



Flanged inlet



Flanged outlet

Pole-Wire	NEMA	V/AC	Color	Plug	Connector	Receptacle	Flanged Inlet	Flanged Outlet
3P-3W	L10-20	125/250	Orange & black	AHCL1020P	AHCL1020C	AHCL1020R	AHCL1020FI	AHCL1020FO
	L11-20	3ØY 250	Blue & black	AHCL1120P	AHCL1120C	AHCL1120R	AHCL1120FI	AHCL1120FO
3P-4W	L14-20	125/250	Orange & black	AHCL1420P	AHCL1420C	AHCL1420R	AHCL1420FI	AHCL1420FO
	L15-20	3ØY 250	Blue & black	AHCL1520P	AHCL1520C	AHCL1520R	AHCL1520FI	AHCL1520FO
	L16-20	3ØY 480	Red & black	AHCL1620P	AHCL1620C	AHCL1620R	AHCL1620FI	AHCL1620FO
4P-4W	L18-20	3ØY 120/208	Blue & black	AHCL1820P	AHCL1820C	AHCL1820R	AHCL1820FI	AHCL1820FO
	L19-20	3ØY 277/480	Red & black	AHCL1920P	AHCL1920C	AHCL1920R	AHCL1920FI	AHCL1920FO
	L20-20	3ØY 347/600	Black & black	AHCL2020P	AHCL2020C	AHCL2020R	AHCL2020FI	AHCL2020FO
4P-5W	L21-20	3ØY 120/208	Blue & black	AHCL2120P	AHCL2120C	AHCL212R	AHCL2120FI	AHCL2120FO
	L22-20	3ØY 277/480	Red & black	AHCL2220P	AHCL2220C	AHCL2220R	AHCL2220FI	AHCL2220FO
	L23-20	3ØY 347/600	Black & black	AHCL2320P	AHCL2320C	AHCL2320R	AHCL2320FI	AHCL2320FO

30A Industrial grade locking devices

Pole-Wire	NEMA	V/AC	Color	Plug	Connector	Receptacle	Flanged Inlet	Flanged Outlet
2P-3W	L5-30	125	Yellow & black	AHCL530P	AHCL530C	AHCL530R	AHCL530FI	AHCL530FO
	L6-30	250	Blue & black	AHCL630P	AHCL630C	AHCL630R	AHCL630FI	AHCL630FO
	L7-30	277	Gray & black	AHCL730P	AHCL730C	AHCL730R	AHCL730FI	AHCL730FO
	L8-30	480	Red & black	AHCL830P	AHCL830C	AHCL830R	AHCL830FI	AHCL830FO

Arrow Hart color coded ultra grip locking devices

30A Industrial grade locking devices

Pole-Wire	NEMA	V/AC	Color	Plug	Connector	Receptacle	Flanged Inlet	Flanged Outlet
3P-3W	L10-30	  L10-30R L10-30P	125/250 Orange & black	AHCL1030P	AHCL1030C	AHCL1030R	AHCL1030FI	AHCL1030FO
	L11-30	  L11-30R L11-30P	3ØY 250 Blue & black	AHCL1130P	AHCL1130C	AHCL1130R	AHCL1130FI	AHCL1130FO
3P-4W	L14-30	  L14-30R L14-30P	125/250 Orange & black	AHCL1430P	AHCL1430C	AHCL1430R	AHCL1430FI	AHCL1430FO
	L15-30	  L15-30R L15-30P	3ØY 250 Blue & black	AHCL1530P	AHCL1530C	AHCL1530R	AHCL1530FI	AHCL1530FO
	L16-30	  L16-30R L16-30P	3ØY 480 Red & black	AHCL1630P	AHCL1630C	AHCL1630R	AHCL1630FI	AHCL1630FO
	L17-30	  L17-30R L17-30P	3ØY 600 Black & black	AHCL1730P	AHCL1730C	AHCL1730R	AHCL1730FI	AHCL1730FO
4P-4W	L18-30	  L18-30R L18-320P	3ØY 120/208 Blue & black	AHCL1830P	AHCL1830C	AHCL1830R	AHCL1830FI	AHCL1830FO
	L19-30	  L19-30R L19-30P	3ØY 277/480 Red & black	AHCL1930P	AHCL1930C	AHCL1930R	AHCL1930FI	AHCL1930FO
	L20-30	  L20-30R L20-30P	3ØY 347/600 Black & black	AHCL2030P	AHCL2030C	AHCL2030R	AHCL2030FI	AHCL2030FO
4P-5W	L21-30	  L21-30R L21-30P	3ØY 120/208 Blue & black	AHCL2130P	AHCL2130C	AHCL2130R	AHCL2130FI	AHCL2130FO
	L22-30	  L22-30R L22-30P	3ØY 277/480 Red & black	AHCL2230P	AHCL2230C	AHCL2230R	AHCL2230FI	AHCL2230FO
	L23-30	  L23-30R L23-30P	3ØY 347/600 Black & black	AHCL2330P	AHCL2330C	AHCL2330R	AHCL2330FI	AHCL2330FO



Plug



Connector



Receptacle



Flanged inlet



Flanged outlet