

HEX WASHER HEAD TEK SCREWS • ZINC

		Best Merchandising Option			
		Plastic Box	Gravity Feed Jar	Job Jar	
Size	Bit Size	Part #	Box Qty/ Std Pk	Part #	Jar Qty/ Std Pk
6-20 x 3/8	1/4"	78606	100/500	▲	—
6-20 x 1/2		78608	100/500	▲	—
6-20 x 5/8		78610	100/500	▲	—
6-20 x 3/4		78612	100/500	▲	—
6-20 x 1		78616	100/500	▲	—
8-18 x 1/2	1/4"	78808	100/500	78808J	100/1200
8-18 x 5/8		78810	100/500	78810J	100/1200
8-18 x 3/4		78812	100/500	78812J	100/1200
8-18 x 1		78816	100/500	78816J	100/1200
8-18 x 1 1/4		78820	100/500	▲	—
8-18 x 1 1/2		78824	100/500	78824J	100/1200
10-16 x 1/2	5/16"	79008	100/500	79008J	100/1200
10-16 x 5/8		79010	100/500	79010J	100/1200
10-16 x 3/4		79012	100/500	79012J	100/1200
10-16 x 1		79016	100/500	79016J	100/1200
10-16 x 1 1/4		79020	100/500	79020J	100/600
10-16 x 1 1/2		79024	50/250	79024J	100/600
10-16 x 1 3/4		79028	50/250	▲	—
10-16 x 2		79032	50/250	79032J	100/600
10-16 x 2 1/2		79040	*100	▲	—
10-16 x 3		79048	*100	79048J	100/600
12-14 x 3/4	5/16"	79212	100/500	79212J	100/1200
12-14 x 1		79216	100/500	79216J	100/1200
12-14 x 1 1/4		79220	50/250	79220J	100/600
12-14 x 1 1/2		79224	50/250	79224J	100/600
12-14 x 2		79232	50/250	79232J	100/600
12-14 x 2 1/2		79240	*100	79240J	100/600
12-14 x 3		79248	*100	79248J	100/600
1/4-14 x 3/4	3/8"	79412	100/500	79412J	100/600
1/4-14 x 1		79416	50/250	79416J	100/600
1/4-14 x 1 1/4		79420	50/250	▲	—
1/4-14 x 1 1/2		79424	50/250	79424J	100/600
1/4-14 x 2		79432	25/125	79432J	100/600
1/4-14 x 2 1/2		79440	*100	▲	—
1/4-14 x 3		79448	*100	▲	—



- #6 Tek Screws feature a #1 drill point.
- #8 and #10 Tek Screws feature a #2 drill point.
- #12 and #14 Tek Screws feature a #3 drill point.

▲ Contact customer service for gravity feed jar availability.

*These items are packaged in cardboard boxes.

Continued on next page.

For bulk packaging, contact customer service for quantities and availability.

HEX WASHER HEAD TEK SCREWS • ZINC (CONT.)

Kits			
Part #	Description		
	Hex Washer Head Tek Kit		
39509 (307 Piece Kit)	8 x 1/2" (100 Pieces)	8 x 3/4" (50 Pieces)	8 x 1" (40 Pieces)
	10 x 1/2" (50 Pieces)	10 x 3/4" (35 Pieces)	10 x 1" (30 Pieces)
	1/4" Mag Tek Driver	5/16" Mag Hex Driver	

HEX WASHER HEAD TEK SCREWS • 410 STAINLESS STEEL



				Best Merchandising Option			
		Plastic Box		Gravity Feed Jar		Job Jar	
Size	Bit Size	Part #	Box Qty/ Std Pk	Part #	Jar Qty/ Std Pk	Part #	Jar Qty
6-20 x 3/8	1/4"	78606SS	100/500	78606SSJ	100/1200	—	—
6-20 x 1		78616SS	100/500	78616SSJ	100/1200	—	—
8-18 x 1/2	1/4"	78808SS	100/500	78808SSJ	100/1200	—	—
8-18 x 1		78816SS	100/500	78816SSJ	100/1200	—	—
10-16 x 1/2	5/16"	79008SS	100/500	79008SSJ	100/1200	—	—
10-16 x 1		79016SS	100/500	79016SSJ	100/1200	—	—
10-16 x 1 1/2		79024SS	50/250	79024SSJ	100/600	—	—
12-14 x 1	5/16"	79216SS	100/500	79216SSJ	100/1200	—	—
12-14 x 1 1/2		79224SS	50/250	79224SSJ	100/600	—	—

Harsh Environment Product

WAFER HEAD LATH TEK SCREWS (K-LATH) • PHILLIPS • ZINC



• Wafer head provides a larger bearing surface.

				Best Merchandising Option			
		Plastic Box		Gravity Feed Jar		Job Jar	
Size	Bit Size	Part #	Box Qty/ Std Pk	Part #	Jar Qty/ Std Pk	Part #	Jar Qty
8 x 1/2	#2	26809	100/500	26809J	100/1200	26809-6	1000
8 x 9/16		26811	100/500	26811J	100/1200	26811-6	1000
8 x 3/4		26813	100/500	26813J	100/1200	26813-6	1000
8 x 1		26817	100/500	26817J	100/1200	26817-6	500
8 x 1 1/4		26821	100/500	26821J	100/1200	26821-6	500

For bulk packaging, contact customer service for quantities and availability.