

Miniature & Automotive Lamps

Miniature Lamps (Alphanumeric)

Ordering Code	Bar Code	Amps	Volts	Base	Filament	MOL	MOD	Life Hours
927	49682	1.2	6	Miniature Wedge (W2.1x9.5d)	C-2R	1.49/37.9	0.62/15.8	50
928	41032	0.3	28	Miniature Wedge (W2.1x9.5d)	C-2F	1.49/37.9	0.62/15.8	500
939	49683	0.9	6	Miniature Wedge (W2.1x9.5d)	C-6	1.49/37.9	0.62/15.8	75
949	49621	0.022	130	Miniature Bayonet (BA9s)	2C-2F	1.19/30.2	0.43/11.0	7000
957	41040	0.5	9.84	Miniature Bayonet (BA9s)	C-2R	1.38/35.1	0.59/15.0	200
967	49622	0.025	120	Miniature Bayonet (BA9s)	CC-7A	1.19/30.2	0.43/11.0	7500
1003	40155	0.94	12.8	SC Bayonet (BA15s)	C-6	1.75/44.5	0.79/20.1	100
1003-BP	40156	0.94	12.8	SC Bayonet (BA15s)	C-6	1.75/44.5	0.79/20.1	100
1003LL-BP	00201	0.94	12.8	SC Bayonet (BA15s)	C-6	1.75/44.5	0.79/20.1	200
1004	40158	0.94	12.8	DC Bayonet (BA15d)	C-6	1.75/44.5	0.79/20.1	200
1004-BP	40159	0.94	12.8	DC Bayonet (BA15d)	C-6	1.75/44.5	0.79/20.1	200
1016	40166	1.34/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	300 / 1000
1016-BP	48083	1.34/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	300 / 1000
1034	40161	1.8/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 5000
1034-BP	49690	1.8/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 5000
1047	16012	2.7	26.0	SC Bayonet (BA15s)	2CC6	2.25/57.2	1.42/36.1	25
1062	49618	0.92	40	DC Bayonet (BA15d)	C-2V	2.25/57.2	1.42/36.1	100
1073	40165	1.8	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1073-BP	49691	1.8	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1076	40167	1.8	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	200
1076-BP	81031	1.8	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	200
1093	49684	1.19	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1000
1105	05147	5.72	6.2	SC Bayonet (BA15s)	C-2V	2.25/57.2	1.42/36.1	125
1129	40170	2.63	6.4	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1129-BP	40103	2.63	6.4	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	200
1130	40172	2.63	6.4	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	200
1133	40174	3.91	6.2	SC Bayonet (BA15s)	C-6	2.25/57.2	1.42/36.1	200
1134	49619	3.91	6.2	DC Bayonet (BA15d)	C-2R	2.25/57.2	1.42/36.1	200
1139IF	00487	1.04	12.8	SC Bayonet (BA15s)	C-6	2.25/57.2	1.42/36.1	700
1141	40176	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1500
1141-BP	41066	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1500
1141IF	40115	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1000
1141LL	42514	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	2000
1141LL-BP	40327	1.6	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	2000
1142	40178	1.6	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	1000
1142-BP	42164	1.6	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	1000
1143	49635	1.98	12.5	SC Bayonet (BA15s)	C-2R	2.25/57.2	1.42/36.1	400
1143IF	49636	1.98	12.5	SC Bayonet (BA15s)	C-2R	2.25/57.2	1.42/36.1	400
1144	49637	1.98	12.5	DC Bayonet (BA15d)	C-2R	2.25/57.2	1.42/36.1	400
1152	40184	1.34	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	500
1154	40186	2.63/0.75	6.4/7	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 1000
1154-BP	40121	2.63/0.75	6.4/7	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 1000
1155	40188	0.59	13.5	SC Bayonet (BA15s)	C-6/C-6	1.44/36.6	0.75/19.1	5000
1155-BP	40189	0.59	13.5	SC Bayonet (BA15s)	C-6/C-6	1.44/36.6	0.75/19.1	5000
1156	40190	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156-BP	40191	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156A	44030	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156A-BP	40215	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156B	00354	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156DC	44334	2.1	12.8	DC Bayonet (BA15d)	C-6	2.00/50.8	1.04/26.4	1200
1156G	00352	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156LL		2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	2400
1156LL-BP	40323	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	2400
1156NA	40193	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156NA-BP	44034	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156P	00355	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156R	00351	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1156Y	00353	2.1	12.8	SC Bayonet (BA15s)	C-6	2.00/50.8	1.04/26.4	1200
1157	40194	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157-BP	40195	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157A	40197	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157A-BP	40198	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157LL	42518	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
1157LL-BP	40321	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
1157NA	40199	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157NA-BP	40200	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	1200 / 5000
1157NALL-BP	40339	2.1/0.59	12.8/14	DC Index Bayonet (BAY15d)	C-6/C-6	2.00/50.8	1.04/26.4	2400 / 10000
1158	40202	2.63/0.75	6.4/7	DC Bayonet (BA15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 1000
1158-BP	42166	2.63/0.75	6.4/7	DC Bayonet (BA15d)	C-6/C-6	2.00/50.8	1.04/26.4	200 / 1000
1176	40204	1.34/0.59	12.8/14	DC Bayonet (BA15d)	C-6/C-6	2.00/50.8	1.04/26.4	300 / 1500
1176-BP	40205	1.34/0.59	12.8/14	DC Bayonet (BA15d)	C-6/C-6	2.00/50.8	1.04/26.4	300 / 1500