








Part Number	Description	Faceview	Part Number	Description	Faceview
DP1-DB9-16LS	Single Outlet 9 Pin D-Sub Size 16 Housing		EP-R-32	Continental European Receptacle 3 AMP Reset Size 32 Housing	
DB25-16LS	25 Pin D-Sub Size 16 Housing		GF-RJ45-USB-AFAF-R-32	GFCI Receptacle RJ45 USB Female Form A to Female Form A 3 AMP Reset Size 32 Housing	
DP1-RJ11-R-16	Single Outlet RJ11 3 AMP Reset Size 16 Housing		GF-DB9-R-32	GFCI Receptacle 9 Pin D-Sub 3 AMP Reset Size 32 Housing	
DP-DB9-R-32	Duplex Receptacle 9 Pin D-Sub No Reset Size 32 Housing		DCH2-RJ45-R-32	China 16 AMP Receptacle RJ45 3 AMP Reset Size 32 Housing	
DP-15R-P32	Duplex Receptacle 15 AMP Reset Size 32 Surface Mount Housing		GF-RJ45-USB-*R-32	GFCI Receptacle RJ45 USB Form A Cable 3 AMP Reset Size 32 Housing	
DB09-2-10LS	2 x 9 Pin D-Sub Size 10 Housing		DP1-DDB15-RJ45-2USB-*R-48	Single Outlet Hi-Density 15 Pin D-Sub RJ45 2 x USB Form A Cables 3 AMP Reset Size 48 Housing	
DB09-4-24LS	4 x 9 Pin D-Sub Size 24 Housing		D-2USB-*10LS	2xUSB Form A Cables Size 10 Housing	
DCH1-RJ45-32	China 10 AMP Receptacle RJ45 Size 32 Housing		GF20-NR-32	20A GFCI Receptacle No Reset Size 32 Housing	
DHDP-DB9-RJ45-R-32	Duplex Receptacle Data Hwy DB9 RJ45 3 AMP Reset Size 32 Housing		DP1-RJ45-USB-*16LS	Single Outlet RJ45 USB Form A Cable Size 16 Housing	

* Length in feet. Standard cable lengths are 3, 6 & 10 feet. Consult factory for other lengths.