

KDR Optimized Line Reactors

480 Volt Low-Z	Part Number	NEC Motor HP	Open		UL Type 1 Enclosed		UL Type 3R Enclosed	
			Weight		Part Number *		Part Number *	
	KDRULA6L	0.5	4		KDRULA6LE01		KDRULA6LE3R	
	KDRULA7L	0.75	4		KDRULA7LE01		KDRULA7LE3R	
	KDRULA8L	1	4		KDRULA8LE01		KDRULA8LE3R	
	KDRULA9L	1.5	4		KDRULA9LE01		KDRULA9LE3R	
	KDRULA1L	2	4		KDRULA1LE01		KDRULA1LE3R	
	KDRULA2L	3	4		KDRULA2LE01		KDRULA2LE3R	
	KDRULA3L	5	4		KDRULA3LE01		KDRULA3LE3R	
	KDRULA4L	7.5	4		KDRULA4LE01		KDRULA4LE3R	
	KDRULA5L	10	5		KDRULA5LE01		KDRULA5LE3R	
	KDRULB2L	15	8		KDRULB2LE01		KDRULB2LE3R	
	KDRULB1L	20	8		KDRULB1LE01		KDRULB1LE3R	
	KDRULD1L	25	10		KDRULD1LE01		KDRULD1LE3R	
	KDRULD2L	30	10		KDRULD2LE01		KDRULD2LE3R	
	KDRULC1L	40	15		KDRULC1LE01		KDRULC1LE3R	
	KDRULF2L	50	25		KDRULF2LE01		KDRULF2LE3R	
	KDRULF4L	60	25		KDRULF4LE01		KDRULF4LE3R	
	KDRULF3L	75	33		KDRULF3LE01		KDRULF3LE3R	
	KDRULH3L	100	46		KDRULH3LE01		KDRULH3LE3R	
	KDRULH2L	125	46		KDRULH2LE01		KDRULH2LE3R	
	KDRULH1L	150	46		KDRULH1LE01		KDRULH1LE3R	
	KDRULG3L	200	74		KDRULG3LE01		KDRULG3LE3R	
	KDRULG1L	250	74		KDRULG1LE01		KDRULG1LE3R	
	KDRULG2L	300	74		KDRULG2LE01		KDRULG2LE3R	
	KDRULJ2L	350	80		KDRULJ2LE01		KDRULJ2LE3R	
	KDRULJ1L	400	80		KDRULJ1LE01		KDRULJ1LE3R	
	KDRULL1L	450	120		KDRULL1LE01		KDRULL1LE3R	
	KDRULL2L	500	120		KDRULL2LE01		KDRULL2LE3R	
	KDRULL3L	600	164		KDRULL3LE01			
	KDRULS1L	700	180		KDRULS1LE01			
	KDRULX2L	800	290		KDRULX2LE01			
	KDRULX3L	900	305		KDRULX3LE01			
	KDRULX1L	1000	317		KDRULX1LE01			
	KDRULY1L	1100	502		KDRULY1LE01			
	KDRULY2L	1250	524		KDRULY2LE01			

Part Numbering System

