



Computer Power Cord, NEMA 5-15P to Right Angle C13 - 10A, 125V, 18 AWG, 14 ft., Black

MODEL NUMBER: P006-014-13RA



Computer power cord with right-angled C13 plug allows connection of a PC, monitor or printer in a tight space or at an awkward angle.

Features

Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment

This desktop computer power cord is designed for computers, monitors, scanners, printers and other compatible peripherals. It features a right-angled C13 end for connecting to a device and a 5-15P plug for connecting to an AC power source. The 14-foot length allows you great flexibility in placing equipment with respect to the power outlet.

Right-Angle PC Power Cable Is Easier to Connect in Tight Spaces The angled C13 connector makes installations easier in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled plug guides the computer power supply cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

Highlights

- Right-angle C13 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering computers, printers and other compatible peripherals
- Adds 14 ft. to your existing power connection to provide flexibility in placing devices
- Ideal replacement for worn-out or missing computer power cable
- NEMA 5-15P plug connects to AC power; C13 plug connects to device's C14 inlet

Applications

- Connect devices like computers, monitors, scanners and printers to a power outlet up to 14 ft. away in your home office, work space or dorm room
- Extend an existing power connection up to 14 ft. to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord
- Power a device located in a hard-to-access area behind a desk or flush against a wall

Package Includes

- P006-014-13RA NEMA 5-15P to Right-Angle C13 Power Extension Cable, 14 ft., Black



Specifications

OVERVIEW	
UPC Code	037332185877
Country/Region	North America
INPUT	
Maximum Input Amps	10
Cable Length (ft.)	14
Cable Length (m)	4.3
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.35 x 18.01 x 1.27
Shipping Dimensions (hwd / in.)	9.98 x 7.09 x 0.50
Shipping Weight (kg)	0.40
Shipping Weight (lbs.)	0.89
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	10 - 85% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13 - RIGHT ANGLE
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No



WARRANTY

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
[https://products/product-certification-agencies](https://products.product-certification-agencies)