

2, 3 and 4-Wire 1 3/8" powerfast® Cordsets

- Male Connector
- IEC IP 68
- 600 VAC/DC



Housing Style	Part Number	Cable	Application	Pinout
GYM..	GYM 24-*M/S600	SOOW CPE Black 2x14 AWG 90°C 13.0 mm OD	2-wire application for extreme conditions	1. BK 2. WH
	GYM 22-*M/S600	SOOW CPE Black 2x12 AWG 90°C 14.8 mm OD		
	GYM 20-*M/S600	SOOW CPE Black 2x10 AWG 90°C 16.5 mm OD		
	GYM 34-*M/S600	SOOW CPE Black 3x14 AWG 90°C 13.7 mm OD	3-wire application for extreme conditions	1. BK 2. WH 3. GN
	GYM 32-*M/S600	SOOW CPE Black 3x12 AWG 90°C 15.5 mm OD		
	GYM 30-*M/S600	SOOW CPE Black 3x10 AWG 90°C 17.0 mm OD		
	GYM 44-*M/S600	SOOW CPE Black 4x14 AWG 90°C 14.8 mm OD	4-wire application for extreme conditions	1. BK 2. GN 3. RD 4. WH
	GYM 42-*M/S600	SOOW CPE Black 4x12 AWG 90°C 16.8 mm OD		
	GYM 40-*M/S600	SOOW CPE Black 4x10 AWG 90°C 18.5 mm OD		

Cordsets

* Length in meters. Standard cable lengths are 2, 4, 5, 6, 8 and 10 meters. Consult factory for other lengths.

Standard housing and coupling nut material is anodized aluminum.