


SPECIFICATIONS	
OPERATING TEMPERATURE	-50°C to +350°C (-58°F to +662°F)
HOUSING MATERIAL	SST, A4 1.4404 (AISI 316L)
SEALING MATERIAL	SST
PRESSURE RESISTANCE	100 BAR
MECHANICAL CONNECTION	1/2 NPT
HOUSING NUT TIGHTENING TORQUE	100 Nm MAX.



SOURCE DRAWING - FOR REFERENCE ONLY

					RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com		
					1.				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT RDS DATE 03/11/13		DESCRIPTION THW-6-N1/2-A4-L400		
					2.										
					3.										
4.		MATERIAL		CONTACT TURCK FOR MORE INFORMATION		APVD K.H.		SCALE 1=1.0		IDENTIFICATION NO. M9910613		REV A			
FINISH		UNIT OF MEASUREMENT INCH [MILLIMETER]				DO NOT SCALE THIS DRAWING									
A	DRAWING RELEASE			RDS	03/11/13										
REV	DESCRIPTION			BY	DATE	ECO NO.					FILE: M9910613		SHEET 1 OF 1		