



- Maintenance-free, electronic horn with a long life duration of up to 5,000 hrs
- Sound output can be set to meet the requirements of the application up to 108 dB
- Integrated bracket for simple wall mounting without additional accessories

**TECHNICAL SPECIFICATIONS:**

Life duration
up to 5,000 hrs

Dimensions (Ø x Height):	134 mm x 340 mm
Housing:	PC/ABS-Blend, grey
Fixing:	Wall mounting, integrated mounting bracket
Installation position:	Sound outlet facing downwards
Connection:	Screw terminal with wire protection max. 1.5 mm ²
Cable entry:	Cable diameter max. 11 mm
Tone frequency:	C. 110 Hz

**ORDER SPECIFICATIONS:**

Voltage	24 V AC/DC	10-48 V AC/DC*	115-230 V AC
Current consumption	55 mA	210 mA	30 mA
	574 000 75	574 000 70	574 000 60

* Current consumption at 10 V / 115 V

**ADDITIONAL INFORMATION:**

State-of-the-art technology is used in the signal horns to guarantee an extremely long life of up to 5,000 hours: the high-volume horn tone is emitted with the aid of sophisticated electronics.

WERMA has intentionally avoided the use of electromechanical components which are susceptible to wear and tear, and has in this way ensured that the long-life horns can be used up to ten times longer than similar conventional electromechanical products.

**TECHNICAL DIAGRAMS:**

see page 307

