

GROOVED STYLE KNOBS



**Molded
Round**

**Black top.
Brass insert.
No marker line.**

PART NO:	QTY./PKG.	DIA.
50-501	1	0.520"
50-503	1	0.710"
50-505	1	0.900"



**Molded
Round**

**Aluminum
inlay top.
Brass insert.
No marker line.**

PART NO:	QTY./PKG.	DIA.
50-551	1	0.520"
50-553	1	0.710"
50-555	1	0.900"



**Taper
Skirt**

**Black top.
Brass insert.
White arrow marker.**

PART NO:	PKG.	DIA.
50-401	1	0.875"
50-403	1	1.125"
50-405	1	1.500"



**Taper
Skirt**

**Aluminum
inlay top.
Brass insert.
White arrow marker.**

PART NO:	QTY./PKG.	DIA.
50-451	1	0.875"
50-453	1	1.125"
50-455	1	1.500"



**Single
Bar**

**Black top.
Brass insert.
White marker line.**

PART NO:	QTY./PKG.	DIA.
50-171	1	0.610"
50-173	1	0.830"



**Single
Bar**

**Aluminum
inlay top.
Brass insert.
White marker line.**

PART NO:	QTY./PKG.	DIA.
50-191	1	0.610"
50-193	1	0.830"

BAR AND POINTER KNOBS

**Black
with
white
marker line.**

PART NO:	QTY./PKG.	DIA.
50-101	1	1.250"
50-102	1	1.500"



**Black
with
white
marker
line.**

PART NO:	QTY./PKG.	DIA.
50-131	1	0.625"
50-132	1	0.750"
50-133	1	0.938"



Black with white marker line.

PART NO:	QTY./PKG.	DIA.
50-151	1	1.500"

SERRATED STYLE KNOBS



**Molded
Round**

**Black top.
No marker line.**

PART NO:	QTY./PKG.	DIA.
50-203	1	0.750"
50-205	1	0.875"
50-207	1	1.125"
50-209	1	1.375"
50-211	1	1.750"



**Molded
Round**

**Aluminum inlay top.
No marker line.**

PART NO:	QTY./PKG.	DIA.
50-253	1	0.750"
50-255	1	0.875"
50-257	1	1.125"
50-259	1	1.375"
50-261	1	1.750"

SOLID ALUMINUM KNOBS



**Narrow
Fluted**

**Natural
aluminum,
Black marker line.**

PART NO:	QTY./PKG.	DIA.
50-903	1	0.750"
50-905	1	0.875"



**Full
Knurled**

**Natural
aluminum,
Black marker line.**

PART NO:	QTY./PKG.	DIA.
50-953	1	0.750"
50-955	1	0.875"

FLUTED STYLE KNOBS



**Taper
Skirt**

**Round
black top.
White marker line
on top and skirt.**

PART NO:	QTY./PKG.	DIA.
50-303	1	0.750"
50-305	1	1.000"
50-307	1	1.250"
50-309	1	1.500"
50-311	1	2.000"



**Taper
Skirt**

**Aluminum
inlay top.
White marker line
on top and skirt.**

PART NO:	QTY./PKG.	DIA.
50-353	1	0.750"
50-355	1	1.000"
50-357	1	1.250"
50-359	1	1.500"
50-361	1	2.000"

SHAFT REDUCER

**Use to reduce shaft
diameter from 1/4"
to 1/8".**



PART NO:	QTY./PKG.
50-1418	1

All Knobs have a 1/4" shaft diameter.

All Knobs are available in bulk quantities: add suffix "B" to part number.