



RIGID & INTERMEDIATE METALLIC CONDUIT FITTINGS


RIGID



TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT (LBS)
---------------	-----------------	-----------------	----------------------

Conduit Nipples

Steel



1/2"XCLOSE	64305	20	1.2
1/2"X1 1/2"	64311	25	2
1/2"X2"	64325	15	2
1/2"X3"	64331	25	4.2
1/2"X4"	64341	15	4.2
1/2"X5"	64351B	25	8.25
1/2"X6"	64361	10	3.9
1/2"X8"	64381B	1	0.5
1/2"X10"	64391B	1	0.7
1/2"X12"	64301B	1	0.8
3/4"XCLOSE	64307	20	1.9
3/4"X2"	64327	15	2.4
3/4"X3"	64332	20	6
3/4"X4"	64342	15	9
3/4"X5"	64352B	25	10.75
3/4"X6"	64362	10	5
3/4"X8"	64382B	1	0.72
3/4"X10"	64392B	1	0.9
3/4"X12"	64302B	1	1.1
1"XCLOSE	64310	15	4
1"X2"	64313	20	2
1"X2 1/2"	64323	15	4
1"X3"	64333	25	9
1"X4"	64343B	25	12.25
1"X5"	64353	10	6.4
1"X6"	64363	6	4.8
1"X8"	64383B	1	1.1
1"X10"	64393B	1	1.3
1"X12"	64303B	1	1.6

CONTINUATION OF CHART AND IMPORTANT APPLICATION, MATERIAL AND CERTIFICATION
NOTES PROVIDED ON NEXT PAGE

1 1/4"XCLOSE	64312	10	2.1
1 1/4"X2"	64314	10	2.6
1 1/4"X3"	64334	5	2.4
1 1/4"X4"	64344B	25	16.5
1 1/4"X5"	64354	6	5
1 1/4"X6"	64364	6	6
1 1/4"X8"	64384B	1	1.4
1 1/4"X10"	64394B	1	1.8
1 1/4"X12"	64308B	1	2.2
1 1/2"XCLOSE	64315	5	1.48
1 1/2"X2"	64615	5	1.7
1 1/2"X3"	64335	10	5.6
1 1/2"X4"	64345B	25	20
1 1/2"X5"	64355B	25	25.75
1 1/2"X6"	64365	4	5
1 1/2"X8"	64385B	1	1.7
1 1/2"X10"	64395B	1	2.2
1 1/2"X12"	64605B	1	2.6
2"XCLOSE	64320	4	1.9
2"X3"	64336	6	5
2"X4"	64346B	25	25.75
2"X5"	64356	6	8
2"X6"	64366	5	3
2"X7"	64676	4	8.5
2"X8"	64386	4	9
2"X10"	64396B	1	2.9
2"X12"	64306B	1	3.5
2 1/2"XCLOSE	64617B	1	0.45
2 1/2"X4"	64347B	1	1.5
2 1/2"X5"	64357B	1	2.0
2 1/2"X6"	64367B	1	2.4
2 1/2"X8"	64387B	1	3.3
2 1/2"X10"	64397B	1	4.25
2 1/2"X12"	64607B	1	5.1
3"XCLOSE	64618B	1	1.2
3"X3"	64338B	1	1.3
3"X4"	64348B	1	2.0
3"X5"	64358B	1	2.6
3"X6"	64368B	1	3.0
3"X8"	64388B	1	4.2
3"X10"	64398B	1	5.3
3"X12"	64608B	1	6.3
3 1/2"XCLOSE	64619B	1	1.6
3 1/2"X4"	64349B	1	2.4
3 1/2"X5"	64359B	1	3.2
3 1/2"X6"	64369B	1	3.75
3 1/2"X8"	64389B	1	5.1
3 1/2"X10"	64399B	1	5.6
3 1/2"X12"	64309B	1	7.9
4"XCLOSE	64620B	1	1.8
4"X4"	64340B	1	2.9
4"X5"	64350B	1	3.8
4"X6"	64360B	1	4.4
4"X8"	64380B	1	6.0
4"X10"	64390B	1	7.75
4"X12"	64300B	1	9.25

APPLICATION: INDOORS OR OUTDOORS. Use to connect two steel outlet boxes or other metal enclosures; use to extend a length of threaded Rigid or IMC conduit. **MATERIAL:** Steel, Zinc Electro-Plate. **MISC:** Consult factory for availability of other sizes. **CERTIFICATIONS:** TO UL AND CSA REQUIREMENTS.