



PAN HEAD FRAMING SCREWS • PHILLIPS • SUPER SHARP • BLACK



- Features sharp point metal piercing tip.
- No pre-drilling.
- Perfect for thin-gauge metal applications (up to 20 gauge).

				Best Merchandising Option			
		Plastic Box		Gravity Feed Jar		Job Jar	
Size	Bit Size	Part #	Box Qty/ Std Pk	Part #	Jar Qty/ Std Pk	Part #	Jar Qty
7 x 7/16	#2	10707	100/500	10707J	100/1200	10707-6	1000

PAN HEAD FRAMING SCREWS • PHILLIPS • TEK • BLACK




- Great for metal-to-metal applications in steel and aluminum up to 12 gauge.

				Best Merchandising Option			
		Plastic Box		Gravity Feed Jar		Job Jar	
Size	Bit Size	Part #	Box Qty/ Std Pk	Part #	Jar Qty/ Std Pk	Part #	Jar Qty
7 x 7/16	#2	10708	100/500	10708J	100/1200	10708-6	1000

For bulk packaging, contact customer service for quantities and availability.

PAN HEAD TEK SCREWS • SQUARE DRIVE • ZINC

				Best Merchandising Option			
		 Plastic Box	 Gravity Feed Jar		 Job Jar		
Size	Bit Size	Part #	Box Qty/ Std Pk	Part #	Jar Qty/ Std Pk	Part #	Jar Qty
6 x 3⁄8	#1	26606	100/500	26606J	100/1200	—	
8 x 1⁄2	#2	26808	100/500	26808J	100/1200	26808-6	1000
8 x 5⁄8		26810	100/500	26810J	100/1200	—	
8 x 3⁄4		26812	100/500	26812J	100/1200	26812-6	750
8 x 1		26816	100/500	26816J	100/1200	26816-6	750
8 x 1¼		26820	100/500	26820J	100/1200	—	
10 x 1⁄2	#2	27008	100/500	27008J	100/1200	27008-6	750
10 x 5⁄8		27010	100/500	27010J	100/1200	—	
10 x 3⁄4		27012	100/500	27012J	100/1200	27012-6	750
10 x 1		27016	100/500	27016J	100/1200	27016-6	500
10 x 1¼		27020	100/500	27020J	100/1200	27020-6	500
10 x 1½		27024	50/250	27024J	100/600	27024-6	350
10 x 2		27032	50/250	27032J	100/600	27032-6	250
12 x 3⁄4	#3	27212	100/500	▲		—	
12 x 1		27216	100/500	27216J	100/1200	—	
12 x 1¼		27220	50/250	▲		—	




 Kits			
Part #	Description		
39505 (381 Piece Kit)	#8 & #10 Pan Head Square Drive Tek Screw Kit Includes a #2-2" Power Bit		
	8 x 1/2" (100 Pieces)	8 x 3/4" (60 Pieces)	8 x 1" (50 Pieces)
	10 x 1/2" (80 Pieces)	10 x 3/4" (50 Pieces)	10 x 1" (40 Pieces)

▲ Contact customer service for gravity feed jar availability.

For bulk packaging, contact customer service for quantities and availability.

PAN HEAD TEK SCREWS • PHILLIPS • ZINC



- #6 Tek Screws feature a #1 drill point.
- # 8 & #10 Tek Screws feature a #2 drill point.

				Best Merchandising Option			
		Plastic Box		Gravity Feed Jar		Job Jar	
Size	Bit Size	Part #	Box Qty/ Std Pk	Part #	Jar Qty/ Std Pk	Part #	Jar Qty
6-20 x ½	#1	82608	100/500	82608J	100/1200	—	—
6-20 x ⅝		82610	100/500	▲		—	—
6-20 x ¾		82612	100/500	82612J	100/1200	—	—
6-20 x 1		82616	100/500	82616J	100/1200	—	—
8-18 x ½	#2	82808	100/500	82808J	100/1200	—	—
8-18 x ⅝		82810	100/500	82810J	100/1200	—	—
8-18 x ¾		82812	100/500	82812J	100/1200	—	—
8-18 x 1		82816	100/500	82816J	100/1200	—	—
8-18 x 1¼		82820	100/500	82820J	100/1200	—	—
8-18 x 1½		82824	100/500	82824J	100/1200	—	—
10-16 x ½	#2	83008	100/500	83008J	100/1200	—	—
10-16 x ⅝		83010	100/500	83010J	100/1200	—	—
10-16 x ¾		83012	100/500	83012J	100/1200	83012-6	500
10-16 x 1		83016	100/500	83016J	100/1200	—	—
10-16 x 1¼		83020	100/500	83020J	100/1200	—	—
10-16 x 1½		83024	50/250	83024J	100/600	—	—



Kits

Part #	Description			
39507 (381 Piece Kit)	#8 & #10 Pan Head Phillips Tek Screw Kit Includes a #2-2" Power Bit			
	8 x ½" (100 Pieces)	8 x ¾" (60 Pieces)	8 x 1" (50 Pieces)	
	10 x ½" (80 Pieces)	10 x ¾" (50 Pieces)	10 x 1" (40 Pieces)	

▲ Contact customer service for gravity feed jar availability.

For bulk packaging, contact customer service for quantities and availability.