

TRADE SIZE	HALEX PART #	PCS/UNIT	CTN/CASE QTY	CTN/CASE WT (LBS)	UPC CODED SELL UNIT
------------	--------------	----------	--------------	-------------------	---------------------

SQUEEZE CONNECTORS (ZINC DIE CAST)

3/8" (1/2 KO)	04203B	BULK	50/500	3.5/35	CARTON
1/2"	04205B	BULK	25/250	2.5/25	CARTON
3/4"	04207B	BULK	25/250	3.3/32.5	CARTON
1"	04210	TRAY BOX	10	1.7	PRODUCT
1"	04210B	BULK	10/100	2/20	NA
1 1/4"	04212	TRAY BOX	5	1.5	PRODUCT
1 1/4"	04212B	BULK	10/100	2.9/29	NA
1 1/2"	04215	TRAY BOX	10	3.6	PRODUCT
1 1/2"	04215B	BULK	5/50	2/19.5	NA
2"	04220	TRAY BOX	4	1.9	PRODUCT
2"	04220B	BULK	10/40	4.6/18.4	NA
2 1/2"	04225B	BULK	10	9	NA
3"	04230B	BULK	5	6.5	NA
3 1/2"	04235B	BULK	2	3	NA
4"	04240B	BULK	1	2	NA

BAGGED ITEMS

3/8"	90420	1/BAG	50 BAGS	3.5	BAG
3/8"	20420	3/BAG	10 BAGS	2	BAG
1/2"	90421	1/BAG	35 BAGS	3.5	BAG
1/2"	20421	3/BAG	15 BAGS	4.2	BAG
3/4"	90422	1/BAG	30 BAGS	3.9	BAG
3/4"	20422	3/BAG	5 BAGS	1.8	BAG

WITH INSULATED THROAT

1/2"	84205B	BULK	25/250	2.5/25	NA
3/4"	84207B	BULK	25/250	3.3/32.5	NA
1"	84210B	BULK	10/100	2/20	NA
1 1/4"	84212B	BULK	10/100	2.9/29	NA
1 1/2"	84215B	BULK	5/50	2/19.5	NA
2"	84220B	BULK	10/40	4.6/18.4	NA

☒ APPLICATION: INDOORS ONLY - In a dry location, use to connect flexible metallic conduit and steel AC cable to a steel outlet box, load center or other metal enclosure. The 3/8" can also be used with steel and aluminum MC cable.

☒ MATERIAL: Zinc Die Cast

☒ MISC: 3/8" size fits 1/2" knockout

☒ SUITABLE FOR: 3/8" steel flexible conduit, #14/2 wire steel armored cable, .561 steel and .538-.599 aluminum interlocked metal clad cable. 1/2" steel flexible metal conduit and #4-2 wire steel armored cable. 3/4" steel flexible metal conduit and #6-3 wire steel armored cable. 1" steel and reduced wall steel flexible metal conduit and #2-2 wire steel armored cable. 1 1/4" - 4" steel flexible metal conduit.

☒ CERTIFICATIONS: UL, CSA.



FLEX-TO-EMT (ZINC DIE CAST) COMBINATION COUPLINGS

COMPRESSION TO SCREW-IN TYPE

1/2"	04905B	BULK	50/500	4/40	NA
3/4"	04907B	BULK	25/250	2.8/27.5	NA
1"	04910	TRAY BOX	10	1.7	PRODUCT

BAGGED ITEMS

1/2"	20491	2/BAG	10 BAGS	1.7	BAG
3/4"	20492	2/BAG	8 BAGS	1.9	BAG

☒ APPLICATION: INDOORS ONLY - Use to join EMT conduit to flexible metallic conduit.

☒ MATERIAL: Zinc Die Cast

☒ TYPE: Compression to Screw-in

☒ SUITABLE FOR: 1/2" steel, steel reduced wall, and aluminum flexible metal conduit to EMT, 3/4"-1" flexible metal conduit to EMT.

☒ CERTIFICATIONS: UL, CSA.

