





TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT(lbs.)	(in inches)	
				A	B
Conduit Bushings			ZINC DIE CAST		
1/2"	05205B	100/1000	3/30	1.05	0.37
3/4"	05207B	100/1000	5/50	1.32	0.37
1"	05210B	50/500	3/30	1.58	0.37
1 1/4"	05212B	25/250	2.5/25	1.94	0.47
1 1/2"	05215B	25/250	3.75/37.5	2.20	0.50
2"	05220B	25/250	4.25/17	2.69	0.52
2 1/2"	05225B	10/100	3.6/36	3.23	0.52
3"	05230B	10/100	4.7/47	3.84	0.85
3 1/2"	05235B	5/50	3.05/30.5	4.35	0.85
4"	05240B	5/50	4/40	5.02	0.85

Application: Indoors or Outdoors. Use with locknut to terminate threaded Rigid or IMC conduit to an outlet box. The rounded surface of the bushing prevents damage to wire insulation. **Material:** Zinc Die Cast



				A	B	C
				THERMOPLASTIC		
1/2"	75205B	100/1000	1/10	0.594	1.063	0.375
3/4"	75207B	100/1000	1/10	0.781	1.281	0.406
1"	75210B	50/500	1/10	1.000	1.563	0.563
1 1/4"	75212B	25/250	.75/7.5	1.313	1.906	0.563
1 1/2"	75215B	25/250	.75/7.5	1.531	2.219	0.563
2"	75220B	25/250	1.5/15	1.969	2.781	0.625
2 1/2"	75225B	10/100	1.1/11	2.406	3.375	0.750
3"	75230B	10/100	1.4/14	3.000	4.083	0.750
3 1/2"	75235B	5/50	1.1/11	3.328	4.469	0.688
4"	75240B	5/50	1.15/11.5	3.875	5.000	0.688

Application: Indoors or Outdoors. Use with locknut to terminate threaded Rigid or IMC conduit to box. Rounded surface of bushing prevents damage to wire insulation. Required by the NEC. **Material:** High Impact Thermoplastic **Features:** Flame-Retardant to 105° C.



				ZINC DIE CAST		
				Insulated Metallic Grounding Bushing (Lay-In Lug)		
1/2"	95205B	25/100	1.38/5.52	1.845	1.063	0.500
3/4"	95207B	25/100	1.75/7	2.047	1.281	0.500
1"	95210B	25/100	2.25/9	2.329	1.531	0.594
1 1/4"	95212B	20	2.6	2.688	1.875	0.625
1 1/2"	95215B	20	3.2	3.109	2.156	0.625
2"	95220B	10	2.1	3.594	2.625	0.625
2 1/2"	95225B	10/40	3.9/15.6	4.485	3.219	0.875
3"	95230B	10/40	5.8/23.2	5.063	3.813	0.875
3 1/2"	95235B	5/20	3.35/13.4	5.610	4.344	0.875
4"	95240B	5/20	4.5/18	6.095	4.813	0.875

Application: Indoors or Outdoors. Use with locknut to terminate service conduit to a cabinet. Lug provided for bonding jumper to a neutral bus bar. Rounded surface of bushing prevents damage to wire insulation. **Material:** Zinc Die Cast **Features:** Thermoplastic liner rated at 150° F

