

TRADE SIZE	HALEX PART #	PCS/ UNIT	CTN/CASE QTY	CTN/CASE WT (LBS)	UPC CODED SELL UNIT
------------	--------------	-----------	--------------	-------------------	---------------------

THREADED CONDUIT BODIES (ALUMINUM) WITH COVER AND GASKET

TYPE: LB

1/2"	58605	TRAY BOX	10	2.7	UPC ON PRODUCT
3/4"	58607	TRAY BOX	10	3.8	UPC ON PRODUCT
1"	58610	TRAY BOX	3	1.9	UPC ON PRODUCT
1 1/4"	58612	TRAY BOX	2	2.6	UPC ON PRODUCT
1 1/2"	58615	TRAY BOX	2	2.7	UPC ON PRODUCT
2"	58620	TRAY BOX	1	2.4	UPC ON PRODUCT
2 1/2"	58625	TRAY BOX	1	6	UPC ON PRODUCT
3"	58630B	BULK	1	5	NA
3 1/2"	58635B	BULK	1	9.5	NA
4"	58640B	BULK	1	8.5	NA

TYPE: T

1/2"	58805	TRAY BOX	5	1.6	UPC ON PRODUCT
3/4"	58807	TRAY BOX	3	1.3	UPC ON PRODUCT
1"	58810	TRAY BOX	2	1.4	UPC ON PRODUCT
1 1/4"	58812	TRAY BOX	2	3.7	UPC ON PRODUCT
1 1/2"	58815	TRAY BOX	2	3.3	UPC ON PRODUCT
2"	58820	TRAY BOX	1	2.5	UPC ON PRODUCT
2 1/2"	58825B	BULK	1	6.222	NA
3"	58830B	BULK	1	6.780	NA
3 1/2"	58835B	BULK	1	12.526	NA
4"	58840B	BULK	1	10.66	NA

TYPE: LR

1/2"	58905	TRAY BOX	5	1.5	UPC ON PRODUCT
3/4"	58907	TRAY BOX	3	1.3	UPC ON PRODUCT
1"	58910	TRAY BOX	2	1.4	UPC ON PRODUCT
1 1/4"	58912	TRAY BOX	2	2.8	UPC ON PRODUCT
1 1/2"	58915	TRAY BOX	2	3.3	UPC ON PRODUCT
2"	58920	TRAY BOX	1	2.7	UPC ON PRODUCT
2 1/2"	58925B	BULK	1	6.000	NA
3"	58930B	BULK	1	6.800	NA
3 1/2"	58935B	BULK	1	11.55	NA
4"	58940B	BULK	1	10.6375	NA

TYPE: LL

1/2"	58305	TRAY BOX	5	1.5	UPC ON PRODUCT
3/4"	58307	TRAY BOX	3	1.3	UPC ON PRODUCT
1"	58310	TRAY BOX	2	1.4	UPC ON PRODUCT
1 1/4"	58312	TRAY BOX	2	2.8	UPC ON PRODUCT
1 1/2"	58315	TRAY BOX	2	3.1	UPC ON PRODUCT
2"	58320	TRAY BOX	1	2.7	UPC ON PRODUCT
2 1/2"	58325B	BULK	1	3	NA
3"	58330B	BULK	1	6.592	NA
3 1/2"	58335B	BULK	1	10.286	NA
4"	58340B	BULK	1	9.8792	NA

TYPE: C

1/2"	58405	TRAY BOX	5	1.4	UPC ON PRODUCT
3/4"	58407	TRAY BOX	3	1.3	UPC ON PRODUCT
1"	58410	TRAY BOX	2	1.2	UPC ON PRODUCT
1 1/4"	58412	TRAY BOX	2	3.3	UPC ON PRODUCT
1 1/2"	58415	TRAY BOX	2	3	UPC ON PRODUCT
2"	58420	TRAY BOX	1	2.6	UPC ON PRODUCT
2 1/2"	58425B	BULK	1	5.682	NA
3"	58430B	BULK	1	6.314	NA
3 1/2"	58435B	BULK	1	9.74	NA
4"	58440B	BULK	1	10.226	NA

☒ APPLICATION: INDOORS OR OUTDOORS. Use to gain access to the interior of a raceway for wire pulling, splicing (with limitations as specified by the NEC), and maintenance.

Not listed for wet locations.

☒ MATERIAL: Copper-Free Die-Cast Aluminum, Aluminum Stamped Cover and Neoprene Gasket

☒ CERTIFICATIONS: UL, CSA.





TRADE SIZE	HALEX PART #	PCS/ UNIT	CTN/CASE QTY	CTN/CASE WT (LBS)	UPC CODED SELL UNIT
------------	--------------	-----------	--------------	-------------------	---------------------

THREADED CONDUIT BODIES (ALUMINUM) COVER & GASKET SOLD SEPARATELY

TYPE: LB

1/2"	59605B	BULK	10/100	2.7/27	NA
3/4"	59607B	BULK	10/50	3.8/19	NA
1"	59610B	BULK	5/25	2.9/14.5	NA
1 1/4"	59612B	BULK	2/10	2.6/13	NA
1 1/2"	59615B	BULK	2/10	1.912/9.56	NA
2"	59620B	BULK	1	2.016	NA

TYPE: T

1/2"	59805B	BULK	10/100	3.2/32	NA
3/4"	59807B	BULK	10/50	4.8/24	NA
1"	59810B	BULK	5/25	3.5/17.5	NA

TYPE: C

1/2"	59405B	BULK	10/100	2.5/25	NA
------	--------	------	--------	--------	----

- ☒ APPLICATION: INDOORS OR OUTDOORS.
- ☒ MATERIAL: Copper-Free Die-Cast Aluminum
- ☒ CERTIFICATIONS: UL, CSA

RGD/EMT COMBO CONDUIT BODIES (ALUMINUM) WITH COVER AND GASKET

TYPE: LR

1/2"	56905	TRAY BOX	10	3	NA
3/4"	56907	TRAY BOX	6	1.8	NA

TYPE: LL

1/2"	56305	TRAY BOX	10	2.7	NA
3/4"	56307	TRAY BOX	6	1.62	NA

TYPE: C

1/2"	56405	TRAY BOX	10	2.5	NA
3/4"	56407	TRAY BOX	6	1.5	NA

TYPE: LB

1/2"	56605	TRAY BOX	10	2.7	NA
3/4"	56607	TRAY BOX	10	3.8	NA

TYPE: T

1/2"	56805	TRAY BOX	10	3.2	NA
3/4"	56807	TRAY BOX	5	1.6	NA

- ☒ APPLICATION: INDOORS OR OUTDOORS. Use to gain access to the interior of a raceway for wire pulling, splicing (with limitations as specified by the NEC), and maintenance. Not listed for wet locations.
- ☒ MATERIAL: Copper-Free Die-Cast Aluminum
- ☒ MISC: Can be used with either Rigid, IMC or EMT conduit.
- ☒ CERTIFICATIONS: UL, CSA.



TRADE SIZE	HALEX PART #	PCS/ UNIT	CTN/CASE QTY	CTN/CASE WT (LBS)	UPC CODED SELL UNIT
---------------	-----------------	--------------	-----------------	----------------------	------------------------

MOGUL PULLING ELBOWS-TYPE LB (ALUMINUM)

1 1/4"	58212B	BULK	5	7	NA
1 1/2"	58215B	BULK	2	7	NA
2"	58220B	BULK	2	7	NA

- ☒ APPLICATION: Indoors or Outdoors. Use to gain access to the interior of a raceway for wire pulling, splicing (with limitations as specified by the NEC), and maintenance.
Not listed for wet locations.
- ☒ MATERIAL: Copper-Free Die-Cast Aluminum
- ☒ MISC: Allows larger access to inside of raceway for easier wire pulling.
- ☒ CERTIFICATIONS: UL, CSA.

