

TRADE SIZE	HALEX PART #	PCS/ UNIT	CTN/CASE QTY	CTN/CASE WT (LBS)	UPC CODED SELL UNIT
------------	--------------	-----------	--------------	-------------------	---------------------

LIQUID-TIGHT CONNECTORS (ZINC DIE CAST) ONE-PIECE

1/2"	06305B	BULK	25/100	3.5/14	NA
3/4"	06307B	BULK	10/100	2.1/21	NA

BAGGED ITEMS

1/2"	90361	1/BAG	15 BAGS	2.1	UPC ON BAG
3/4"	90362	1/BAG	10 BAGS	2.1	UPC ON BAG

WITH INSULATED THROAT

1/2"	86305B	BULK	25/100	3.5/14	NA
3/4"	86307B	BULK	10/100	2.1/21	NA

☒ APPLICATION: INDOORS OR OUTDOORS. Use to connect flexible metallic or type B non-metallic liquid-tight conduit to a steel outlet box or other metal enclosure or hub.

☒ MATERIAL: Zinc Die Cast

☒ FEATURES: New one-piece design allows for quick and easy installation. Push in and twist conduit counter-clockwise until seated. Tighten screw to 35 in-lbs. and install into enclosure. It's that easy!

☒ CERTIFICATIONS: UL Canadian/US.



LIQUID-TIGHT CONNECTORS (ZINC DIE CAST) MULTI-PIECE

3/8" (1/2 KO)	16203B	BULK	25/100	5/20	NA
1/2"	16205B	BULK	25/100	4.3/17	NA
3/4"	16207B	BULK	10/100	2.5/25	NA
1"	16210B	BULK	10/100	4.4/44	NA
1"	16210	1/BAG	10 BAGS	4.4	UPC ON BAG
1 1/4"	16212B	BULK	4/40	2.7/26.8	NA
1 1/2"	16215B	BULK	2/20	1.8/18.4	NA
2"	16220B	BULK	2/20	2.8/28	NA

BAGGED ITEMS

1/2"	91625	1/BAG	20 BAGS	4	UPC ON BAG
3/4"	91627	1/BAG	15 BAGS	3.4	UPC ON BAG

WITH INSULATED THROAT

3/8" (1/2 KO)	96203B	BULK	25/100	5/20	NA
1/2"	96205B	BULK	25/100	4.3/17	NA
3/4"	96207B	BULK	10/100	2.5/25	NA
1"	96210B	BULK	10/100	4.4/44	NA
1 1/4"	96212B	BULK	4/40	2.7/26.8	NA
1 1/2"	96215B	BULK	2/20	1.8/18.4	NA
2"	96220B	BULK	2/20	2.8/28	NA
2 1/2"	96225B	BULK	1	2.7	NA
3"	96230B	BULK	1	3.06	NA
3 1/2"	96235B	BULK	1	3.80	NA
4"	96240B	BULK	1	4.31	NA

☒ APPLICATION: INDOORS OR OUTDOORS. Use to connect flexible metallic or type B non-metallic liquid-tight conduit to a steel outlet box or other metal enclosure or hub.

☒ MATERIAL: Zinc Die Cast

☒ MISC: 3/8" size fits 1/2" knockout.

☒ CERTIFICATIONS: UL, CSA.

