


TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT (LBS)	DIMENSIONS (IN INCHES)		
				A	B	C
QUICK-SET® Liquid-Tight Connectors				Nylon		
3/8"(1/2"ko)	76203B	25	1.5	1.18	0.55	1.42
1/2"	76205B	25/100	1.5/15	1.18	0.55	1.42
3/4"	76207B	10/100	0.7/7	1.20	0.64	1.69
1"	76210B	5/50	0.6/6	1.23	0.72	2.02
1 1/4"	76212B	5/25	1.082/5.41	2.44	0.76	2.40
1 1/2"	76215B	2/10	0.50/2.50	2.70	0.80	2.67
2"	76220B	2/10	0.86/4.33	2.99	0.85	3.28

APPLICATION: INDOORS OR OUTDOORS. Use to connect type B non-metallic liquid-tight conduit to a weatherproof outlet box, pool/spa equipment motor, central air conditioning unit or various other electrical enclosures or hubs. **MATERIAL:** Nylon. **FEATURES:** Fitting will not rust or corrode. **No disassembly required, just insert conduit, then hand-tighten nut.** Reusable. **MISC:** 3/8" size fits 1/2" knockout. **CERTIFICATIONS:** TO UL AND CSA REQUIREMENTS.



TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT (LBS)	DIMENSIONS (IN INCHES)		
				A	B	C
QUICK-SET® 90° Liquid-Tight Connectors				Nylon		
3/8"(1/2"ko)	76903B	10/100	0.8/7.2	2.84	0.50	2.03
1/2"	76905B	10/100	0.8/7.2	2.84	0.50	2.03
3/4"	76907B	10/100	1/10	3.25	0.50	2.33
1"	76910B	5/50	0.9/9	3.54	0.60	2.95
1 1/4"	76912B	5/25	0.9/9	4.75	0.76	5.20
1 1/2"	76915B	2/10	0.9/9	4.75	0.80	5.20
2"	76920B	2/10	0.9/9	5.42	0.86	5.80

APPLICATION: INDOORS OR OUTDOORS. Use to connect type B non-metallic liquid-tight conduit to a weatherproof outlet box, pool/spa equipment motor, central air conditioning unit or various other electrical enclosures or hubs. **MATERIAL:** Nylon. **FEATURES:** Fitting will not rust or corrode. **No disassembly required, just insert conduit, then hand-tighten nut.** Reusable. **MISC:** 3/8" size fits 1/2" knockout. **CERTIFICATIONS:** TO UL AND CSA REQUIREMENTS.



TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT (LBS)	DIMENSIONS (IN INCHES)		
				A	B	C
Screw-In Couplings				PVC		
1/2"	74505B	30	0.3			
3/4"	74507B	25	0.4			

APPLICATION: INDOORS OR OUTDOORS. Use to connect two lengths of type B non-metallic liquid-tight conduit. **MATERIAL:** PVC. **FEATURES:** Screw-in type. **CERTIFICATIONS:** TO UL AND CSA REQUIREMENTS.

