



AD2240W1  
AD2241W1



WS2000W  
WS1000W



WS1020NW  
WS1021NW



DT2000W



WSTA120



DT5030W

## Dual (Ultrasonic and Passive Infrared)

24V DC, 33mA. Requires a CU300xx series control unit.

| Description                    | Color        | Single Circuit | Dual Circuit |
|--------------------------------|--------------|----------------|--------------|
|                                |              | 1 button       | 2 buttons    |
| Selectable Manual/<br>Auto ON. | Black        | AD2240BK1      | AD2240BK2    |
|                                | Gray         | AD2240GY1      | AD2240GY2    |
|                                | Ivory        | AD2240I1       | AD2240I2     |
|                                | Light Almond | AD2240LA1      | AD2240LA2    |
|                                | White        | AD2240W1       | AD2240W2     |
| Manual ON (Vacancy).           | Black        | AD2241BK1      | AD2241BK2    |
|                                | Gray         | AD2241GY1      | AD2241GY2    |
|                                | Ivory        | AD2241I1       | AD2241I2     |
|                                | Light Almond | AD2241LA1      | AD2241LA2    |
|                                | White        | AD2241W1       | AD2241W2     |

Note: Wallplate sold separately. See page E-23 for technical specifications, coverage patterns and wiring schematics.

## Passive Infrared

Manual time delay adjustment.

| Description                                                                                                  | Color        | Standard | with Nightlight | with Neutral | with Nightlight<br>and Neutral |
|--------------------------------------------------------------------------------------------------------------|--------------|----------|-----------------|--------------|--------------------------------|
| Manual adjusting; selectable<br>manual/auto ON operation;<br>dual-voltage 120/277V AC;<br>multi-way capable. | Gray         | WS2000GY | WS2000NGY       | —            | —                              |
|                                                                                                              | Ivory        | WS2000I  | WS2000NI        | WS2004I      | WS2004NI                       |
|                                                                                                              | Light Almond | WS2000LA | WS2000NLA       | —            | —                              |
|                                                                                                              | White        | WS2000W  | WS2000NW        | WS2004W      | WS2004NW                       |
| Manual adjusting; selectable<br>manual/auto ON operation;<br>120V AC only.                                   | Ivory        | WS1000I  | WS1000NI        | —            | —                              |
|                                                                                                              | Light Almond | WS1000LA | WS1000NLA       | —            | —                              |
|                                                                                                              | White        | WS1000W  | WS1000NW        | —            | —                              |
| Manual adjusting;<br>manual ON operation;<br>120V AC only.                                                   | Ivory        | WS1001I  | WS1001NI        | —            | —                              |
|                                                                                                              | Light Almond | WS1001LA | WS1001NLA       | —            | —                              |
|                                                                                                              | White        | WS1001W  | WS1001NW        | —            | —                              |
| Manual adjusting;<br>auto ON operation;<br>dual circuit;<br>120V AC only.                                    | Gray         | WS1020GY | WS1020NGY       | —            | —                              |
|                                                                                                              | Ivory        | WS1020I  | WS1020NI        | WS1024I      | WS1024NI                       |
|                                                                                                              | Light Almond | WS1020LA | WS1020NLA       | WS1024LA     | WS1024NLA                      |
|                                                                                                              | White        | WS1020W  | WS1020NW        | WS1024W      | WS1024NW                       |
| Manual adjusting;<br>manual ON operation;<br>dual circuit;<br>120V AC only.                                  | Gray         | WS1021GY | WS1021NGY       | —            | —                              |
|                                                                                                              | Ivory        | WS1021I  | WS1021NI        | WS1025I      | WS1025NI                       |
|                                                                                                              | Light Almond | WS1021LA | WS1021NLA       | WS1025LA     | WS1025NLA                      |
|                                                                                                              | White        | WS1021W  | WS1021NW        | WS1025W      | WS1025NW                       |

Note: See page E-24 for technical specifications, coverage patterns and wiring schematics.

## Digital Timer

| Description                                                                                                                              | Color | Catalog Number |
|------------------------------------------------------------------------------------------------------------------------------------------|-------|----------------|
| DIP switch enable preset intervals for 2 and 4 hours. User adjustable up to 24 hours. 3-way capable, 960W @ 120V AC and 1200W @ 277V AC. | White | DT2000W        |

## Programmable Timer

| Description                                                                                                                                                                                               | Color | Catalog Number |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|----------------|
| Wall Switch Programmable Timer with Astronomical Clock, Features 3 Interchangeable cover colors: Gray, Light Almond and White. Compatible in SP and 3-Way configurations, 120V AC, neutral wire required. | White | WSTA120        |

## Count Down Timers

| Description                             | Color        | 30 Minutes:<br>OFF, 5, 10, 20, 30 | 60 Minutes:<br>OFF, 15, 30, 45, 60 | 12 Hours:<br>OFF, 2, 4, 8, 12 |
|-----------------------------------------|--------------|-----------------------------------|------------------------------------|-------------------------------|
|                                         |              |                                   |                                    |                               |
| 1000W @ 120V AC and<br>1400W @ 277V AC. | Ivory        | DT5030I                           | DT5060I                            | DT5012I                       |
|                                         | Light Almond | DT5030LA                          | DT5060LA                           | DT5012LA                      |
|                                         | White        | DT5030W                           | DT5060W                            | DT5012W                       |