

Installation Accessories

Unless indicated otherwise, accessories can be used with either poly or metal plugs and receptacles

Handles



NPT	Poly Handle Threaded Opening	Metal Handle* Threaded Opening	90° Nylon Handle Threaded Opening
1/2"	01-NA013-12	H091U12	04-2A090-5-12
3/4"	01-NA013-34	H091U34	04-2A090-5-34
1"	01-NA013-1	H091U1	04-2A090-5-10

Cable Range	Nylon Handle	Angled Nylon Handle
.35 - .70	01-NA013	01-NA313

- Notes:**
- For available cord grips, see pgs 193-194.
 - * For metal devices only

NPT Guidelines

Cable Range	NPT
.062 - .5	1/2"
.187 - .75	3/4"
.437 - 1.10	1"
.750 - 1.375	1 1/4"

NPT sizes are determined by the cable diameter and third party cord grip.

Junction Boxes



30.0 in³*



26.9 in³*



6.9 in³*



3.4 in³*



3.7 in³*



84.2 in³*

NPT	Metal Box	Metal Box Nylon Angle 30°	Metal Box Metal Angle 45°	Poly Conduit* Entry	Poly Straight* Wall Box	Metal Straight Wall Box	Poly 70°** Wall Box
1/2"	MB312	01-NA053-080-12	09-NA053-080-12	01-NA023-12	01-NA025-12	09-NA025-12	51-AA058
3/4"	MB334	01-NA053-080-34	09-NA053-080-34	01-NA023-34	01-NA025-34	09-NA025-34	51-AA058
1"	MB31	01-NA053-080-1	09-NA053-080-1	—	—	—	51-AA058
1 1/4"	MB3114	01-NA053-080-114	09-NA053-080-114	—	—	—	51-AA058

* For poly devices only

** 70° boxes are not drilled. Contact customer service if factory drilling is required.

* Interior volume with receptacle installed.

Angles



Nylon 30° Angle	Nylon 30° Angle for MB Box	Metal 45° Angle	Metal Straight Adapter	Metal 30° Angle/Adapter Plate for FS Box
01-NA027	01-NA027-601	09-NA027	MSPN	MAFS1*

* Includes angle, adapter plate and gaskets for FS box mounting

Miscellaneous Accessories



For Male Devices Only



Protective Cap	Flush Mount	Cord Grip with Mesh	Multi-Contact Removal Tool	Crimper Tool (Greenlee or equal)	European Crimping Tool
01-NA126	01-2A142	see pgs 193-194	9-LD12-37	4CN30	61-CA500

Order Example

A typical order should include an inlet part number, a receptacle part number **AND** the matching handles, angles or other required accessories.



Male Inlet with Handle (Plug)
07-A8001 + 01-NA313



Female Receptacle with Angle Adapter
07-A4001 + 01-NA027