

CATALOG NUMBER	CONDUCTOR RANGES IN CIRCULAR MILS 		DIMENSIONS			INSTALLATION TOOLING (# OF CRIMPS)				WIRE STRIP LENGTH
	MIN.	MAX.	L ± .05	O.D. ± .01	WALL ± .008	DIE TYPE	HYDRAULIC TOOLS			
							Y35, Y39, Y750 PAT35, PAT750		Y46  	
YSM29-2	211,500	275,000	1.38 [35]	.75 [19]	.077 [2]	NEST INDENTOR	U29D1 (1) Y34PR11	U29D1 (1) Y34PR11	1-7/16"	
YSM30-2	250,000	330,000	1.38 [35]	.81 [21]	.081 [2]	NEST INDENTOR	U30D1 (1) Y34PR11	U30D1 (1) Y34PR11	1-7/16"	
YSM31-2	270,000	385,000	1.50 [38]	.88 [22]	.087 [2]	NEST INDENTOR	U31D1 (1) Y34PR11	U31D1 (1) Y34PR11	1-9/16"	
YSM32-2	290,000	440,000	1.50 [38]	.95 [24]	.095 [2]	NEST INDENTOR	U32D1 (1) Y34PR11	U32D1 (1) Y34PR11	1-9/16"	
YSM33-2	350,000	495,000	1.50 [38]	1.01 [26]	.104 [3]	NEST INDENTOR	U33D1 (1) Y34PR11	U33D1 (1) Y34PR11	1-9/16"	
YSM34-2	400,000	550,000	1.62 [41]	1.06 [27]	.113 [3]	NEST INDENTOR	U34D1 (1) Y34PR11	U34D1 (1) Y34PR11	1-11/16"	
YSM35-2	440,000	605,000	1.62 [41]	1.12 [28]	.125 [3]	NEST INDENTOR	U35D1 (1) Y34PR11	U35D1 (1) Y34PR11	1-11/16"	
YSM36-2	480,000	660,000	1.62 [41]	1.19 [30]	.132 [3]	NEST INDENTOR	----- -----	P36D (1) P48PR2	1-11/16"	
YSM38-2	600,000	770,000	1.88 [48]	1.25 [32]	.133 [3]	NEST INDENTOR	----- -----	P38D (1) P48PR2	1-15/16"	
YSM40-2	675,000	880,000	1.88 [48]	1.35 [34]	.149 [4]	NEST INDENTOR	----- -----	P40D (1) P48PR2	1-15/16"	
YSM41-2	800,000	935,000	1.88 [48]	1.38 [35]	.153 [4]	NEST INDENTOR	----- -----	P41D (1) P48PR2	1-15/16"	
YSM44-2	800,000	1,100,000	1.88 [48]	1.49 [38]	.164 [4]	NEST INDENTOR	----- -----	P44D (1) P48PR2	1-15/16"	


NOTES:

1. MATERIAL: COPPER.
2. FINISH: TIN PLATED.
3. CATALOG NUMBER PUADP-1 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 HYPRESS™ .
4. CATALOG NUMBER Y35P3 ADAPTOR DIE IS REQUIRED FOR Y34PR11 INDENTOR.
5. FOR ADDITIONAL INSTALLATION TOOLING REFER TO FACTORY.
6. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
7. MIXED CONDUCTOR RANGE ACCOMMODATED BY CONNECTOR BARRELS. THESE REPRESENT TOTALS FOR PARALLEL HYLINKS™.
8. WHEN INSTALLING MIXED CONDUCTOR COMBINATIONS, IDENT INTO STRANDED CABLES WHILE LOCATING MAGNET WIRES IN NEST DIE AREA.
9. SPLICING OF MIXED COMBINATIONS OF COPPER MAGNET WIRE AND COPPER STRANDED CABLES.


SUGGESTED METHOD OF SELECTING CONNECTOR AND INSTALLATION TOOLING:

DETERMINE CROSS SECTION (CIRCULAR MIL AREA) OF CONDUCTORS. COMPARE TOTAL AREA WITH THE MIN-MAX RANGES AS SHOWN IN TABLE. SELECT CONNECTOR WHICH ACCEPTS THE CONDUCTORS WITH OPTIMUM SNUG FIT. IF THERE IS AN EXCESS OF VOIDS AROUND THE MAGNET WIRES THEY SHOULD BE PRE-SHAPED FOR FIT INTO A SMALLER CONNECTOR. AN ALTERNATE METHOD OF REDUCING VOIDS BETWEEN COPPER STRAPS IS BY ADDING COPPER FILLERS. USE NEST AND INDENTOR DIES WITH ASSOCIATED CONNECTORS AS OUTLINED IN TABLE. TRIAL INSTALLATIONS SHOULD BE CROSS SECTIONED THROUGH DEEPEST PORTION OF INDENT AND SHOULD REVEAL A MINIMUM OF VOIDS BETWEEN CONDUCTORS. CONTACT BURNDY® IF A CONNECTOR RECOMMENDATION CANNOT BE RESOLVED.


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
E	03/12/2013	REDRAW YSM SALES DRAWING & COMBINE SHEETS. CHANGE DWG. FORMAT, "FCI" IS SHOWN IN UPPER PORTION OF TITLE BLOCK, REMOVE IT.	30841	GP	MB




ISOMETRIC VIEW



LAP SPLICE
(TYPICAL INSTALLATION)



TYPICAL STAMPING



SUPERSEDES: SD56814

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	PARALLEL HYLINK™				
	ITEM NO: N/A				
	CAT. NO: YSM--- 2 (TABLE)				
	DRAWN BY: J. WALTERS		09/30/1997		
	CHECKER: --		--		
	DSN APRVL: K. WOO		03/25/1997		
	MFG APRVL: --		--		
	QA APRVL: J. BRODEUR		09/23/1997		
	MKT APRVL: G. SCHWEBLER		09/23/1997		
	PROD FAM: --		--		DRAWING NO
PROJECT #: --		SIZE		SC041139	E
DOCUMENT TYPE: SALES		D		SHEET 2 OF 2	
REL LEVEL: Released					