

Rigid/Intermediate Grade Conduit Fittings

- Conduit Bushed Nipples
- 90° Pull Elbows
- Offset Conduit Nipples

- Knockout Snap-In Blanks
- Push Plugs

CP

CONDUIT BUSHED NIPPLES – DIE CAST ZINC

Non-Insulated
UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	50D	1/2"	100	1000	4
	51D	3/4"	50	500	5
	52D	1"	25	250	10
	53D	1 1/4"	25	100	11
	54D	1 1/2"	25	100	20
	55D	2"	10	40	30
	56D	2 1/2"	10	40	40
	57D	3"	10	40	49
	58D	3 1/2"	10	40	68
	59D	4"	5	20	70

90 DEGREE PULL ELBOWS – MALLEABLE IRON

Features:

- Raintight
- Furnished with Neoprene gasketed steel cover
- Furnished with Steel lock nut
- Furnished with Stamped Steel cover
- Threaded for rigid conduit and IMC
- For outdoor use
- Standard Finish: Zinc plated

(Gasketed – Liquidtight)

Male To Female
UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	810	1/2"	20	100	34
	811	3/4"	10	50	56
	812	1"	5	25	88
	813	1 1/4"	2	10	92
	814	1 1/2"	2	10	200
	815	2"	1	5	344

Female To Female
UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	820	1/2"	20	100	36
	821	3/4"	10	50	49
	822	1"	5	25	94
	823	1 1/4"	2	10	140
	824	1 1/2"	2	10	200
	825	2"	1	5	344

90 DEGREE PULL ELBOWS – DIE CAST ZINC

(Gasketed – Liquidtight)

Male To Female; Combination Rigid and EMT
UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	810DC	1/2"	10	100	31
	811DC	3/4"	5	50	31
					

Female To Female; Combination Rigid and EMT

UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	820DC	1/2"	10	100	28
	821DC	3/4"	5	50	35
	822DC	1"	5	25	64
	823DC	1 1/4"	2	20	66

OFFSET CONDUIT NIPPLES – MALLEABLE IRON

Features:

- Threaded NPSM for rigid conduit and IMC
- Standard Finish: Zinc Plated
- USE: To offset the axis of raceways 3/4 of an inch

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	300	1/2"	25	100	24
	301	3/4"	25	100	34
	302	1"	10	50	49
	303	1 1/4"	10	50	54

OFFSET CONDUIT NIPPLES – DIE CAST ZINC

UL File No. E-19189

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	300DC	1/2"	10	100	9
	301DC	3/4"	10	100	15
	302DC	1"	10	100	21
	303DC	1 1/4"	5	50	33
	304	1 1/2"	5	50	40
	305	2"	2	20	65


KNOCKOUT SNAP-IN BLANKS – STEEL

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	335	1/2"	100	1000	2
	336	3/4"	100	1000	2
	337	1"	50	500	2
	338	1 1/4"	50	250	3
	339	1 1/2"	25	250	5
	340	2"	20	200	7

PUSH PLUGS – PLASTIC*

	Cat. #	Size	Unit Quantity	Standard Package	Weight Lbs. Per 100
	PPC-50	1/2"	100	1000	1
	PPC-75	3/4"	100	1000	1
	PPC-100	1"	50	500	1
	PPC-125	1 1/4"	50	200	1
	PPC-150	1 1/2"	25	100	1
	PPC-200	2"	25	100	1
	PPC-250	2 1/2"	—	100	2
	PPC-300	3"	—	100	3
	PPC-350	3 1/2"	—	50	6
	PPC-400	4"	—	50	8

*Temperature Rating: 180° – 200°F
Tensile Strength: 600 – 2300 PSI



TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT(lbs.)
---------------	-----------------	-----------------	----------------------

DIMENSIONS
(in inches)
A B

EMT-to-EMT Pull Elbows

ZINC DIE CAST

WITHOUT GASKET



1/2"	14405	15	2.8	1.31	0.97
3/4"	14407	10	3.7	1.50	1.20

WITH NEOPRENE GASKET

1/2"	94405	10	2.4	1.31	.97
3/4"	94407	5	1.9	1.50	1.20
1"	94410	5	3.4	1.85	1.52

Application: Dry Locations. Use to connect EMT conduit together at a 90° bend.

Material: Zinc Die Cast **Type:** Set-Screw Type **Features:** Removable aluminum cover facilitates wire pulling.



TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT(lbs.)
---------------	-----------------	-----------------	----------------------



EMT-to-Box Pull Elbows

ZINC DIE CAST

WITHOUT GASKET

1/2"	14305	10	2.2	1.31	0.97
3/4"	14307	5	1.8	1.50	1.20

Application: Dry Locations. Use to connect EMT conduit to a metal box or enclosure to form a 90° bend. **Material:** Zinc Die Cast **Type:** Set-Screw Type **Features:** Removable aluminum cover facilitates wire pulling. Die cast locknut provided.




EMT-to-EMT Inside-Corner Pull Elbows






ZINC DIE CAST

1/2"	14605	15	2.7	1.81	1.00
3/4"	14607	8	1.9	2.00	1.25

Application: Indoors Only. Use to connect EMT conduit together on a 90° inside corner.

Material: Zinc Die Cast **Type:** Set-Screw Type **Features:** Removable cover facilitates wire pulling.






DIMENSIONS (in inches)


TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT(lbs.)	A	B	C
Rigid Three-Piece Couplings				MALLEABLE IRON		
1/2"	65505B	25	6.9	1.188	0.984	1.406
3/4"	65507B	25	8.1	1.375	1.125	1.641
1"	65510B	10	6.3	1.688	0.750	2.016
1 1/4"	65512B	10	9.8	2.063	1.500	2.516
1 1/2"	65515B	10	13.5	2.344	1.672	2.828
2"	65520B	10	18.7	3.000	1.781	3.359
2 1/2"	65525B	10	33.5	3.500	1.938	4.031
3"	65530B	1	4	4.125	2.250	4.531
3 1/2"	65535B	1	5.8	4.688	2.594	5.297
4"	65540B	1	7.6	5.406	3.078	5.719

Application: Indoors or Outdoors. Use as a threaded coupling between lengths of threaded Rigid or IMC conduit, when neither can be rotated. **Material:** Malleable Iron



Rigid-to-Rigid Pull Elbows				ZINC DIE CAST	
WITH NEOPRENE GASKET					
1/2"	94105B	10/100	2.8/28	1.31	1.02
3/4"	94107B	5/50	1.7/17	1.50	1.27
1"	94110	5	3.1	1.85	1.54

Application: Indoors or Outdoors. Use as a wire pulling elbow to facilitate wire pulling through a sharp bend in a run of threaded Rigid or IMC conduit. Removable cover provides easy access to facilitate wire pulling. **Material:** Zinc Die Cast



Rigid-to-Box Pull Elbows				ZINC DIE CAST	
WITH GASKET					
1/2"	94205B	10/100	3.1/31	1.31	1.02
3/4"	94207B	5/50	1.85/18.5	1.50	1.27
WITHOUT GASKET					
1/2"	14205	10	3.1	1.31	1.02
3/4"	14207	5	1.85	1.50	1.27

Application: Indoors or Outdoors. Use to connect a run of threaded Rigid or IMC conduit to an outlet box or other metal enclosure. Removable cover provides easy access to facilitate wire pulling. **Material:** Zinc Die Cast

