

Routing, Protection and Insulation

Spiralwrap


Spiralwrap - Special Materials

Flame Retardant Polyethylene Spiralwrap

HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize. Suitable for applications requiring a self-extinguishing material. Lower cost than polyamide 6 or Teflon materials. Natural color is milky white.

Features and Benefits

- Sheathing allows flexible routing and lead-out of cables
- The inner edges are beveled preventing damage to cables
- Sheathing is reusable and resistant to most chemicals



MATERIAL	Polyethylene, flame retardant (PE-FR)
Flammability	UL 94 V2
Operating Temperature	-4°F to +176°F (-20°C to +80°C)

RoHS

PART NO.	TYPE	Diameter (D) in. (mm)	Wall Thickness (WT) in. (mm)	Pitch in. (mm)	Min. Bundle Diameter in. (mm)	Max. Bundle Diameter in. (mm)	Color	Pkg. Qty.
1FRP0C	1FRP	0.13 (3.18)	0.032 (0.81)	0.19 (4.75)	0.06 (1.6)	0.50 (12.7)	Black	100 ft
1FRP9C*		0.13 (3.18)	0.032 (0.81)	0.19 (4.75)	0.06 (1.6)	0.50 (12.7)	Natural	100 ft
2FRP0C*	2FRP	0.25 (6.35)	0.045 (1.14)	0.38 (9.53)	0.18 (4.75)	2.00 (50.8)	Black	100 ft
2FRP9C*		0.25 (6.35)	0.045 (1.14)	0.38 (9.53)	0.18 (4.75)	2.00 (50.8)	Natural	100 ft
2.5FRP0C	2.5FRP	0.38 (9.53)	0.052 (0.81)	0.44 (11.13)	0.31 (7.92)	3.00 (76.2)	Black	100 ft
2.5FRP9C*		0.38 (9.53)	0.052 (0.81)	0.44 (11.13)	0.31 (7.92)	3.00 (76.2)	Natural	100 ft
3FRP0C*	3FRP	0.50 (12.7)	0.062 (1.57)	0.56 (14.3)	0.37 (9.52)	4.00 (102.0)	Black	100 ft
3FRP9C*		0.50 (12.7)	0.062 (1.57)	0.56 (14.3)	0.37 (9.52)	4.00 (102.0)	Natural	100 ft
4FRP0C	4FRP	0.75 (19.05)	0.065 (1.65)	0.75 (19.05)	0.75 (19.05)	5.00 (127.0)	Black	100 ft
4FRP9C*		0.75 (19.05)	0.065 (1.65)	0.75 (19.05)	0.75 (19.05)	5.00 (127.0)	Natural	100 ft
161-05084	5FRP	1.00 (25.4)	0.095 (2.41)	1.00 (25.4)	1.00 (25.4)	7.00 (178.0)	Black	100 ft
5FRP9C*		1.00 (25.4)	0.095 (2.41)	1.00 (25.4)	1.00 (25.4)	7.00 (178.0)	Natural	100 ft

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.