


ZL-AB

Strain Relief Plates for Screw Assembly



Inlay bushings also available in brass.



Type	Order No. for M4 screws	Order No. for M5 screws	Order No. for M6 screws	Length L1	Length L2	No. of teeth	PU
ZL 39 AB	32270	32280 32360	32290	38.5 mm	19.5 mm	3	10
ZL 60 AB	32271	32281 32361	32291	59.5 mm	43.5 mm	4	10
ZL 70 AB	32272	32282 32362	32292	69.1 mm	43.5 mm	5	10
ZL 87 AB	32273	32283 32363	32293	86.5 mm	68 mm	6	10
ZL 103 AB	32275	32284 32364	32294	102.5 mm	84 mm	7	10
ZL 121 AB	32277	32285 32365	32295	121 mm	102.5 mm	8	10
ZL 140 AB	32274	32286 32366	32296	139.5 mm	121 mm	9	10
ZL 180 AB	32276	32287 32367	32297	180 mm	157 mm	12	10


Product Description

The strain relief plate ZL-AB is used for static or dynamic applications for organizing and securing cables on machines, control panels or cable carriers.

By using aluminum / brass nuts for the screw holes, a better fit of the strain relief plate is achieved, even in high vibration environments.

Advantages & Benefits

- Strain relief according to EN 62444
- Easy assembly
- Cost-effective
- High cable density
- Wide variety of mounting options



Specifications

Material	ZL: Polyamide (PA) Bushing: ■ Aluminum ■ Brass (BR)
Flame class	UL94-Vo
Temperature	- 40°C to + 140°C (static) - 40°F to + 284°F (static)
Properties	Halogen-free, silicone-free

Accessories