



MDC (M12) Series Receptacles

2, 4 & 5 Conductor MDC Series Receptacles, 18/22AWG



Back Mount Receptacles | PG9 & M20 Threads | 300 Volt, 4 amps | IP67 Rating




# of Poles	Male Faceview	Color Code	Rating	Wire AWG	PG9 Threads		M20 Threads	
					Male Receptacles	Female Receptacles	Male Receptacles	Female Receptacles
2		3. Brown 4. Blue	300V 4A	18	MDC-2MR-BM-18	MDC-2FR-BM-18	MDC-2MR-M20-BM-18	MDC-2FR-M20-BM-18
				22	MDC-2MR-BM	MDC-2FR-BM	MDC-2MR-M20-BM	MDC-2FR-M20-BM
3		1. Brown 3. Blue 4. Black	300V 4A	18	MDC-3MR-BM-18	MDC-3FR-BM-18	MDC-3MR-M20-BM-18	MDC-3FR-M20-BM-18
				22	MDC-3MR-BM	MDC-3FR-BM	MDC-3MR-M20-BM	MDC-3FR-M20-BM
4		1. Brown 2. White 3. Blue 4. Black	300V 4A	18	MDC-4MR-BM-18	MDC-4FR-BM-18	MDC-4MR-M20-BM-18	MDC-4FR-M20-BM-18
				22	MDC-4MR-BM	MDC-4FR-BM	MDC-4MR-M20-BM	MDC-4FR-M20-BM
5		1. Brown 2. White 3. Blue 4. Black 5. Gray	300V 4A	18	MDC-5MR-BM-18	MDC-5FR-BM-18	MDC-5MR-M20-BM-18	MDC-5FR-M20-BM-18
				22	MDC-5MR-BM	MDC-5FR-BM	MDC-5MR-M20-BM	MDC-5FR-M20-BM

12" leads are standard. Longer lead lengths are available, please consult the factory for part numbers.


Specifications:

Shell: Nickel Plated Brass
Insulator: Polyamide
Wire: 18, 22 & 24 AWG: 300V,
UL Style 1007/1569
Contacts: Copper Alloy with Gold Plating
O-Ring: NBR
Jam Nut: Nickel Plated Brass
Temperature: -40°C to 105°C (-40°F to +221°F)

PG9 Threads




Male Receptacle




Female Receptacle

M20 Threads



Male Receptacle



Female Receptacle

H

Micro-DC (M12) Series Receptacles