



Selection diagram



—●— product options

→ accessory sold separately



Code structure

Attention! The feasibility of a code number does not mean the effective availability of a product. Please contact our sales office.

article options options
FR 502-W3XGM2K70R23T6

Housing

FR technopolymer, one conduit entry

Contact blocks

5	1NO+1NC, snap action
6	1NO+1NC, slow action
7	1NO+1NC, slow action, overlapped
...	

Actuators

01	short plunger
02	roller lever
05	angled roller lever
...	

Reset

	without reset (standard)
W3	simultaneous reset
W4	simultaneous reset, increased force

External metallic parts

	zinc-plated steel (standard)
X	stainless steel

Ambient temperature

	-25°C ... +80°C (standard)
T6	-40°C ... +80°C

Pre-installed cable glands or connectors

	without cable gland or connector (standard)
K23	cable gland for cables Ø 6...Ø 12 mm
K70	M12 plastic connector, 4 poles

Please contact our technical service for the complete list of possible combinations.

Threaded conduit entry

M2	M20x1.5 (standard)
M1	M16x1.5
	PG 13.5
A	PG 11
M3	1/2 NPT

Contact type

	silver contacts (standard)
G	silver contacts with 1 µm gold coating (not for contact block 2)

Rollers

	standard roller
R28	stainless steel, Ø 12 mm (for actuators A4, 15)
R23	stainless steel, Ø 14 mm (for actuators A2, 02, A5, 05, 30, 31, 51, 52, 54, 55, 56, 57)
R24	stainless steel, Ø 20 mm (for actuators 30, 31, 51, 52, 54, 55, 56, 57)
R25	technopolymer, Ø 35 mm (for actuators 30, 31, 51, 52, 54, 55, 56, 57)
R5	rubber, Ø 40 mm (for actuators 30, 31, 51, 52, 54, 55, 56, 57)
R26	rubber, Ø 50 mm (for actuators 51, 52, 54, 55, 56, 57)
R27	rubber, protruding, Ø 50 mm (for actuators 55, 56)