







MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS	
 1 = BLACK 2 = WHITE 3 = GREEN		 1 = BLACK 2 = WHITE 3 = GREEN		CONTACT CARRIER MATERIAL	RUBBER
				CONTACT MATERIAL/PLATING	GOLD-PLATED BRASS
				COUPLING NUT MATERIAL/PLATING	ALUMINUM/ANODIZED
				RATED CURRENT [A]	18.0 A
				RATED VOLTAGE [V]	600 V
				OUTER JACKET MATERIAL/COLOR	RUBBER/BLACK
				CONDUCTOR INSULATION MATERIAL	XLPE
				NUMBER OF CONDUCTORS [AWG]	3x14 AWG
				DRAIN/SHIELD	NONE
				PROTECTION CLASS	IEC IP68
				TEMPERATURE	-40°C TO +105°C (-40°F TO +221°F)



CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

- NOTES:
1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
2. "/S600" DESIGNATES HEAVY DUTY RUBBER INSULATION MATERIAL.

SOURCE DRAWING - FOR REFERENCE ONLY

NOTES: 1."*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS. 2. "/S600" DESIGNATES HEAVY DUTY RUBBER INSULATION MATERIAL.					<table><tr><td>8-29mm</td><td>±1.0mm</td></tr><tr><td>30-49mm</td><td>±2.0mm</td></tr><tr><td>50-69mm</td><td>±3.0mm</td></tr><tr><td>70-100mm</td><td>±4.0mm</td></tr><tr><td>OVER 100mm</td><td>±5.0mm</td></tr></table>		8-29mm	±1.0mm	30-49mm	±2.0mm	50-69mm	±3.0mm	70-100mm	±4.0mm	OVER 100mm	±5.0mm									
8-29mm	±1.0mm																								
30-49mm	±2.0mm																								
50-69mm	±3.0mm																								
70-100mm	±4.0mm																								
OVER 100mm	±5.0mm																								
<table><tr><td colspan="2">RELATED DOCUMENTS</td></tr><tr><td>1.</td><td></td></tr><tr><td>2.</td><td></td></tr><tr><td>3.</td><td></td></tr><tr><td>4.</td><td></td></tr></table>		RELATED DOCUMENTS		1.		2.		3.		4.		<table><tr><td colspan="2">3RD ANGLE PROJECTION</td></tr><tr><td colspan="2"></td></tr></table>		3RD ANGLE PROJECTION				<table><tr><td colspan="2">THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2">3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</td></tr></table>		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.				3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
RELATED DOCUMENTS																									
1.																									
2.																									
3.																									
4.																									
3RD ANGLE PROJECTION																									
																									
THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.																									
																									
3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com																									
<table><tr><td colspan="2">MATERIAL</td></tr><tr><td colspan="2">SEE SPECIFICATIONS</td></tr></table>		MATERIAL		SEE SPECIFICATIONS		<table><tr><td colspan="2">ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</td></tr><tr><td colspan="2">CONTACT TURCK FOR MORE INFORMATION</td></tr></table>		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		CONTACT TURCK FOR MORE INFORMATION		<table><tr><td>DRFT</td><td>JB</td><td>DATE</td><td>11/24/03</td><td colspan="2" rowspan="2">DESCRIPTION GYM GKM 34-*M/S600</td></tr><tr><td>DSGN</td><td></td><td>SCALE</td><td>1 = 1.5</td></tr></table>		DRFT	JB	DATE	11/24/03	DESCRIPTION GYM GKM 34-*M/S600		DSGN		SCALE	1 = 1.5		
MATERIAL																									
SEE SPECIFICATIONS																									
ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY																									
CONTACT TURCK FOR MORE INFORMATION																									
DRFT	JB	DATE	11/24/03	DESCRIPTION GYM GKM 34-*M/S600																					
DSGN		SCALE	1 = 1.5																						
<table><tr><td colspan="2">FINISH</td></tr><tr><td colspan="2">SEE SPECIFICATIONS</td></tr></table>		FINISH		SEE SPECIFICATIONS		<table><tr><td colspan="2">UNIT OF MEASUREMENT</td></tr><tr><td colspan="2">MILLIMETER [INCH]</td></tr><tr><td colspan="2">DO NOT SCALE THIS DRAWING</td></tr></table>		UNIT OF MEASUREMENT		MILLIMETER [INCH]		DO NOT SCALE THIS DRAWING		<table><tr><td colspan="2">IDENTIFICATION NO.</td><td>REV B</td></tr><tr><td colspan="2">FILE: 777002747</td><td>SHEET 1 OF 1</td></tr></table>		IDENTIFICATION NO.		REV B	FILE: 777002747		SHEET 1 OF 1				
FINISH																									
SEE SPECIFICATIONS																									
UNIT OF MEASUREMENT																									
MILLIMETER [INCH]																									
DO NOT SCALE THIS DRAWING																									
IDENTIFICATION NO.		REV B																							
FILE: 777002747		SHEET 1 OF 1																							
<table><tr><td>B</td><td>UPDATE CABLE DIAMETER, SEE ECO</td><td>RWC</td><td>02/05/07</td><td>17143</td></tr><tr><td>REV</td><td>DESCRIPTION</td><td>BY</td><td>DATE</td><td>ECO NO.</td></tr></table>		B	UPDATE CABLE DIAMETER, SEE ECO	RWC	02/05/07	17143	REV	DESCRIPTION	BY	DATE	ECO NO.														
B	UPDATE CABLE DIAMETER, SEE ECO	RWC	02/05/07	17143																					
REV	DESCRIPTION	BY	DATE	ECO NO.																					