





MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS	
 1 = BLACK 2 = GREEN 3 = RED 4 = WHITE		 1 = BLACK 2 = GREEN 3 = RED 4 = WHITE		CONTACT CARRIER MATERIAL	RUBBER
				CONTACT MATERIAL/PLATING	GOLD-PLATED BRASS
				COUPLING NUT MATERIAL/PLATING	ALUMINUM/ANODIZED
				RATED CURRENT [A]	15.0 A
				RATED VOLTAGE [V]	600 V
				OUTER JACKET MATERIAL/COLOR	RUBBER/BLACK
				CONDUCTOR INSULATION MATERIAL	XLPE
				NUMBER OF CONDUCTORS [AWG]	4x14 AWG
				DRAIN/SHIELD	NONE
				PROTECTION CLASS	IEC IP68
				TEMPERATURE	-40°C TO +105°C (-40°F TO +221°F)



CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

- NOTES:
1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
2. "/S600" DESIGNATES HEAVY DUTY RUBBER INSULATION MATERIAL.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
1. 2. 3. 4.				DRFT JBU		DATE 11/26/03	
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DSGN		SCALE 1=1.5	
FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT		DESCRIPTION	
SEE SPECIFICATIONS				MILLIMETER [INCH]		GYM GKM 44-*M/S600	
SEE SPECIFICATIONS				DO NOT SCALE THIS DRAWING		IDENTIFICATION NO.	
						REV	
						B	
B UPDATE CABLE DIAMETER, SEE ECO		RWC 02/05/07 17143				FILE: 777002851	
REV DESCRIPTION		BY DATE ECO NO.				SHEET 1 OF 1	