

DINKLE ENTERPRISE CO., LTD.

No.19, Wuquan 2nd Road., Wugu District,
New Taipei City 248020, Taiwan
TEL:+886-2-8069-9000 7705-6900
FAX:+886-2-2290-1702
E-mail:service@dinkle.com
Web:www.dinkle.com

DINKLE INTERNATIONAL CO., LTD.

No.19, Wuquan 2nd Road., Wugu District,
New Taipei City 248020, Taiwan
TEL:+886-2-8069-9000 7705-6900
FAX:+886-2-2290-1702
E-mail:service@dinkle.com
Web:www.dinkle.com

OPTIKLE INTERNATIONAL CO., LTD.

Room 29, 1/F, Block B, Proficient Industrial Center,
No.6 Wang Kwun Road, Kowloon Bay, Kowloon,
Hong Kong
TEL:+852-2795-3840 2758-8005
FAX:+852-2753-6919
E-mail: Service.LY.Sales@dinkle.com.cn
Web:www.dinkle.com

DINKLE ELECTRIC MACHINERY (CHINA) CO., LTD.

No.388, Xingpu Mid Road, Shipu, Qiandeng Town,
Kunshan City, Jiangsu Province 215343, China
TEL:+86-512-5708-8588
FAX:+86-512-5708-8600
E-mail:Service.SH.Sales@dinkle.com.cn
Web: www.dinkle.com/kscn/

LIYANG ELECTRIC MACHINERY (DONGGUAN) CO., LTD.

No.2, Jinqianlin 1st Street, Jitigang Village, Huangjiang Town,
Dongguan City, Guangdong Province, China
TEL:+86-769-8336-4350 8336-4370
FAX:+86-769-8336-4314
E-mail:Service.LY.Sales@dinkle.com.cn
Web:www.dinkle.com/cn/



E-mail : service@dinkle.com

Web : www.dinkle.com

DINKLE CORPORATION, USA

13748 Pike Road, Missouri City, Texas, USA 77489
TEL:+1-832-539-4703
Toll-Free:+1-844-273-1850
FAX:+1-832-532-7226
E-mail:Service.US.Sales@dinkle.com
Web:www.dinkle.com/en/home

DINKLE S.R.L., ITALY

Via Stabilini n°14, 23864 Malgrate (LC), Italia
TEL:+39/03411716154
E-mail: Service.It.Sales@dinkle.com
Web:www.dinkle.com/it/

DINKLE ELECTRIC TRADING (SHANGHAI) CO., LTD.

Unit 3706, Grand Gateway Tower 2, No. 3 Hongqiao Road,
Xuhui District, Shanghai City.
TEL:+86-21-6487-0636 6487-5423
FAX:+86-21-3356-2500
E-mail: Service.SH.Sales@dinkle.com.cn
Web: www.dinkle.com/cn/


Beijing Sales Office

TEL:+86-10-5873-4338
FAX:+86-10-5873-4337
E-mail: Service.SH.Sales@dinkle.com.cn
Web: www.dinkle.com/cn/

Xi An Sales Office

TEL:+86-29-8885-8475
FAX:+86-21-3356-2500
E-mail: Service.SH.Sales@dinkle.com.cn
Web: www.dinkle.com/cn/

Terminal Block



Dinkle remains the right of product modification and engineering change of design.
The catalogue is for reference only. The final product is made according to actual
engineering drawing.

弊社標準品に関しては、修正や設計変更等が行われるため、カタログは参考であり、
詳細仕様は図面を基準とする。


本公司對產品保有修改、設變權，目錄僅供參考，實際產品仍需依照工程圖面
為準。

JUL ./2023_V.02

Company Profile



Founded in 1983, Dinkle now has been a leading global manufacturer of electrical connection and components for industrial automation technology and contributes in developing and manufacturing products for electrical connectivity, electrical cabinets and communication electronics. With over 400 engineers in the R&D center, all components are manufactured in-house to ensure the outstanding product performance and quality. All production sites are granted by ISO9001 and ISO 14001 and the products are certified by safety approvals of UL, VDE, TUV, ENEC and LR.



Push-in Design Terminal Blocks



Feed-through Terminal Blocks

DP..N		
	1.5 mm ²	P.3
	2.5 mm ²	P.3
	4 mm ²	P.3
	6 mm ²	P.4
DP..		
	10 mm ²	P.4
	16 mm ²	P.4

Feed-through Grounding Terminal Blocks

DP..N-PE		
	1.5 mm ²	P.9
	2.5 mm ²	P.9
	4 mm ²	P.9
	6 mm ²	P.10
DP..-PE		
	10 mm ²	P.10
	16 mm ²	P.10

Feed-through 3-Conductor Terminal Blocks

DP..N-TN		
	1.5 mm ²	P.5
	2.5 mm ²	P.5
	4 mm ²	P.5
	6 mm ²	P.6
DP..-TN		
	10 mm ²	P.6

Feed-through 3-Conductor Grounding Terminal Blocks

DP..N-TN-PE		
	1.5 mm ²	P.11
	2.5 mm ²	P.11
	4 mm ²	P.11
	6 mm ²	P.12
DP..-TN-PE		
	10 mm ²	P.12

Feed-through 4-Conductor Terminal Blocks

DP..N-TR		
	1.5 mm ²	P.7
	2.5 mm ²	P.7
	4 mm ²	P.7
	6 mm ²	P.8

Feed-through 4-Conductor Grounding Terminal Blocks

DP..N-TR-PE		
	1.5 mm ²	P.13
	2.5 mm ²	P.13
	4 mm ²	P.13
	6 mm ²	P.14

Feed-through Multi-Level Terminal Blocks

DPP..N		
	1.5 mm ²	P.15
	2.5 mm ²	P.16
	4 mm ²	P.16
	2.5 mm ²	P.16

Multi-Level Terminal Blocks with Equipotential Bonder

DPP..N-PV		
	1.5 mm ²	P.17
	2.5 mm ²	P.17
	4 mm ²	P.17
	2.5 mm ²	P.18

Multi-Level Terminal Blocks with PE Foot

DPP..N-..L2PE		
	1.5 mm ²	P.19
	2.5 mm ²	P.19
	4 mm ²	P.19
	DP2.5N-3L-L3PE	P.20
	DP2.5N-3L-SPE	P.20
	DP4N-3L-SPE	P.20

Multi-Level Grounding Terminal Blocks

DPP..N-PE		
	1.5 mm ²	P.21
	2.5 mm ²	P.21
	4 mm ²	P.21
	DP2.5N-3L-PE	P.22

Push-in Design Terminal Blocks



Bi-Level Diode Terminal Blocks

	DPP2.5N-D01	P.23
	DPP2.5N-D02	P.24
	DPP2.5N-D03	P.24
	DPP2.5N-D04	P.24

Potential distribution Terminal Blocks

	DPD6-P001	P.26
	DPD6-P002	P.26
	DPD10-P001	P.27
	DPD16-P001	P.27
	DKD35-P001	P.27
	DKD35-P002	P.28
	DKD35-P003	P.28

Sensor / Actuator Terminal Blocks

	DP2.5SGQK01	P.29
	DP2.5SGQK02	P.30
	DP2.5SGQK03	P.30
	DP2.5SGQK04	P.30
	DP2.5SGQK05	P.30
	DP2.5SG	P.31
	DP2.5SGT	P.31
	DP2.5SGC-PE	P.31
	DP2.5SGR	P.32
	DP2.5SGRT	P.32
	DP2.5SGRC-PE	P.32
	0207-01XX	P.32

Plug-in Connection Terminal Blocks

	DPES2.5QK01	P.33
	DPES2.5QK02	P.34
	DPES2.5QK03	P.34
	DPES2.5QK04	P.34
	DPES2.5QK05	P.34
	DPES2.5	P.35
	DPES2.5-PE	P.35
	DP2.5PG-XXP	P.35

Knife and Disconnect Terminal Blocks

DP..N-TP		
	2.5 mm ²	P.37
	4 mm ²	P.38
DP..N-TG		
	2.5 mm ²	P.37
	4 mm ²	P.38
DP..N-CP		
	2.5 mm ²	P.37
	4 mm ²	P.38

Bi-Level Knife and Disconnect Terminal Blocks

DPP..N-TP		
	2.5 mm ²	P.39
DPP..N-TG		
	2.5 mm ²	P.39
DPP..N-CP		
	2.5 mm ²	P.39

Lever-Type Fuse Disconnect Terminal Blocks

	DP4N-TF(5X20)	P.41
	DP4N-TFLXX(5X20)	P.41
	DP6N-TF-6.3X32	P.41
	DP6N-TFLXX-6.3X32	P.42
	DP4N-TFH(5X20)	P.42
	DP4N-TFHLXX(5X20)	P.42

Fuse Disconnect Terminal Blocks

	DP4N-TFU	P.43
	DP4N-TFULXX	P.43
	DP4N-TFU(5X20)	P.44
	DP4N-TFULXX(5X20)	P.44

Test Disconnect Terminal Blocks

	DPTD6N	P.45
	DPTL6N	P.45



Diode Terminal Blocks

	DPTD6N-D05	P.46
	DPTD6N-D06	P.46

Push-in Design Terminal Blocks



Feed-through Multi-Level Terminal Blocks

	DPP2.5N-L24	P.16			
	DPP2.5N-L110	P.16			
	DPP2.5N-L220	P.16			

Sensor / Actuator Terminal Blocks

	DP2.5SG-L24	P.31
---	-------------	------

Sensor / Actuator Terminal Blocks

	DP2.5SGR-L24	P.32
---	--------------	------

Sensor / Actuator Terminal Blocks

	DP2.5SGT-L24	P.31
---	--------------	------

Sensor / Actuator Terminal Blocks

	DP2.5SGRT-L24	P.32
---	---------------	------

Spring Clamp Terminal Blocks



Feed-through Terminal Blocks

	AK..	
	1.5 mm ²	P.49
	2.5 mm ²	P.49
	4 mm ²	P.49
	6 mm ²	P.50
	10 mm ²	P.50
	16 mm ²	P.50
	35 mm ²	P.50

Feed-through Grounding Terminal Blocks

	AK...-PE	
	1.5 mm ²	P.55
	2.5 mm ²	P.55
	4 mm ²	P.55
	6 mm ²	P.56
	10 mm ²	P.56
	16 mm ²	P.56

Feed-through 3-Conductor Terminal Blocks

	AK...-TN	
	1.5 mm ²	P.51
	2.5 mm ²	P.51
	4 mm ²	P.51
	6 mm ²	P.52
	10 mm ²	P.52
	16 mm ²	P.52

3-Conductor Grounding Terminal Blocks

	AK...-TN-PE	
	1.5 mm ²	P.57
	2.5 mm ²	P.57
	4 mm ²	P.57
	6 mm ²	P.58
	10 mm ²	P.58

Feed-through 4-Conductor Terminal Blocks

	AK...-TR	
	1.5 mm ²	P.53
	2.5 mm ²	P.53
	4 mm ²	P.53
	6 mm ²	P.54

4-Conductor Grounding Terminal Blocks

	AK...-TR-PE	
	1.5 mm ²	P.59
	2.5 mm ²	P.59
	4 mm ²	P.59
	6 mm ²	P.60

Bi-Level Terminal Blocks

	AKK1.5	P.61
	AKK2.5	P.62
	AKK4	P.62
	AKK2.5-PV	P.62
	AKK2.5-PE	P.62

Bi-Level Diode Terminal Blocks

	AKK2.5-D01	P.63
	AKK2.5-D02	P.64
	AKK2.5-D03	P.64
	AKK2.5-D04	P.64

Spring Clamp Terminal Blocks



Knife and Disconnect Terminal Blocks

	AK...-TP	
	2.5 mm ² 4 mm ²	P.66 P.67
	AK...-TG	
	2.5 mm ² 4 mm ²	P.66 P.67
	AK...-CP	
	2.5 mm ² 4 mm ²	P.66 P.67

3-Conductor Knife and Disconnect Terminal Blocks

	AK...-TN-TP	
	2.5 mm ²	P.68
	AK...-TN-TG	
	2.5 mm ²	P.68
	AK...-TN-CP	
	2.5 mm ²	P.68


4-Conductor Knife and Disconnect Terminal Blocks

	AK...-TR-TP	
	2.5 mm ²	P.69
	AK...-TR-TG	
	2.5 mm ²	P.69

Fuse Disconnect Terminal Blocks

	AK...-TR-CP	
	2.5 mm ²	P.69
	AK4-TF..	
	AK4-TF(5X20) AK4-TFLXX(5X20)	P.70 P.70

Screw Connection Terminal Blocks



Feed-through Terminal Blocks

	DK...N	
	2.5 mm ²	P.73
	4 mm ²	P.73
	6 mm ²	P.73
	10 mm ²	P.74
	16 mm ²	P.74
	35 mm ²	P.74
	DK...H	
	16 mm ² 35 mm ²	P.75 P.75
	DK...	
	50 mm ²	P.76
	95 mm ²	P.76
	150 mm ²	P.76
	240 mm ²	P.76

Feed-through Grounding Terminal Blocks

	DK...N-PE	
	2.5 mm ²	P.79
	4 mm ²	P.79
	6 mm ²	P.79
	10 mm ²	P.80
	16 mm ²	P.80
	DK...-PE	
	2.5 mm ²	P.81
	4 mm ²	P.82
	10 mm ²	P.82
	16 mm ²	P.82
	35 mm ²	P.80
	50 mm ²	P.81
	95 mm ²	P.81

Screw Connection Terminal Blocks



Feed-through 3-Conductor Terminal Blocks

DK..N-TN		
	2.5 mm²	P.77
	4 mm²	P.77
	6 mm²	P.77
	10 mm²	P.78

Feed-through 4-Conductor Terminal Blocks

DK..N-TR		
	2.5 mm²	P.78
	4 mm²	P.78

Bi-Level Terminal Blocks

DKK..N		
	2.5 mm²	P.83
	4 mm²	P.84

DKK..N-PV		
	2.5 mm²	P.84
	4 mm²	P.84

Bi-Level Grounding Terminal Blocks

DKK..N-L2PE		
	2.5 mm²	P.85
	4 mm²	P.85

DKK..N-PE		
	2.5 mm²	P.85
	4 mm²	P.86

Bi-Level Diode Terminal Blocks

	DKK2.5N-D01	P.87
	DKK2.5N-D02	P.88
	DKK2.5N-D03	P.88
	DKK2.5N-D04	P.88

Sensor / Actuator Terminal Blocks

	DK1.5SG	P.90
	DK1.5SGF	P.90
	DK1.5SGF-PE	P.90
	DK1.5SG-L24	P.90

Plug-in Connection Terminal Blocks

	DKES1.5	P.91
	DKES1.5-XXP	P.91
	DKES1.5M-XXP	P.91

--	--	--

Knife and Disconnect Terminal Blocks

DK..N-TP		
	2.5 mm²	P.93
	4 mm²	P.94

DK..N-TG		
	2.5 mm²	P.93
	4 mm²	P.94

DK..N-CP		
	2.5 mm²	P.93
	4 mm²	P.94

Bi-Level Knife and Disconnect Terminal Blocks

DKK..N-TP		
	2.5 mm²	P.95
	4 mm²	P.96

DKK..N-TG		
	2.5 mm²	P.95
	4 mm²	P.96

DKK..N-CP		
	2.5 mm²	P.95
	4 mm²	P.96


Lever-Type Fuse Disconnect Terminal Blocks

	DK4N-TF(5X20)	P.97
	DK4N-TFLXX(5X20)	P.97
	DKK4N-TF(5X20)	P.97
	DKK4N-TFLXX(5X20)	P.98

Fuse Disconnect Terminal Blocks

	DK10-TF(5X20)	P.99
	DK10-TFA(5X20)	P.99

Screw Connection Terminal Blocks



Test Disconnect Terminal Blocks

	DKTD6N	P.100
---	--------	-------

Miniature Feed-through Terminal Blocks

DK..S		
	2.5 mm²	P.101
	4 mm²	P.101
	6 mm²	P.101

Stud Terminal Blocks



Bolt Connection Terminal Blocks (1500V)

DKM..		
	25 mm²	P.105
	35 mm²	P.105
	50 mm²	P.105
	70 mm²	P.106
	95 mm²	P.106
	120 mm²	P.106
	150 mm²	P.107
	185 mm²	P.107
	240 mm²	P.107

Quick Wiring Terminal Blocks (1500V)

DKM..-U		
	25 mm²	P.109
	35 mm²	P.109
	50 mm²	P.109
	70 mm²	P.110
	95 mm²	P.110
	120 mm²	P.110
	150 mm²	P.111
	185 mm²	P.111
	240 mm²	P.111

Single-Bolt Connection Terminal Blocks (1000V)

DKM..		
	5 (16 mm²)	P.112
	6 (35 mm²)	P.112
	8 (50 mm²)	P.112
	10 (120 mm²)	P.113
	12 (120 mm²)	P.113

--	--	--

Barrier Connection Terminal Blocks



Quick Wiring Terminal Blocks

DKU..		
	15 (1.5 mm²)	P.117
	20 (2.5 mm²)	P.117
	30 (4 mm²)	P.118
	40 (6 mm²)	P.118
	60 (16 mm²)	P.118

DKUU..		
	20 (2.5 mm²)	P.117

--	--	--

Screw Connection Terminal Blocks

DKB..N		
	15 (1.5 mm²)	P.119
	20 (2.5 mm²)	P.119
	30 (4 mm²)	P.120
	40 (6 mm²)	P.120
	60 (16 mm²)	P.120

DKB		
	80 (25 mm²)	P.121
	100 (50 mm²)	P.121
	150 (70 mm²)	P.121
	200 (95 mm²)	P.122
	300 (240 mm²)	P.122
	500 (300 mm²)	P.122

DKBB..		
	10 (2.5 mm²)	P.119

Busbar Clamps

Busbar Clamps			Busbar Holders		
DKZ..			DSH..		
	6 mm²	P.124		DSH1	P.125
	16 mm²	P.124		DSH2	P.125
	35 mm²	P.124		DSHG	P.125
	70 mm²	P.124~P.125			
	120 mm²	P.125			

Wire-to-Wire Connectors

Push-in Design Connectors			Screw Design Connectors		
	0126-11XX	P.128		ECSH381VM-XXPQK01	P.130
				ECSH116VM-XXPQK01	P.130
				2ESDHM-XXPQK01	P.130
				3ESDHM-XXPQK01	P.130
DIN Rail Connectors				2EHDRD	P.131
 	0229-M5XXY	P.129		2EHDRDM	P.131
	0161-12XXQK01	P.129			

Panel Installation Terminal Blocks

Quick Wring Terminal Blocks			Screw Connection Terminal Blocks		
DKUP..-XXPK			DKB..N-XXPCK		
	15 (1.5 mm²)	P.135		15 (1.5 mm²)	P.137
	20 (2.5 mm²)	P.135		20 (2.5 mm²)	P.137
	30 (4 mm²)	P.136		30 (4 mm²)	P.138
	40 (6 mm²)	P.136		40 (6 mm²)	P.138
	60 (16 mm²)	P.136		60 (16 mm²)	P.138
DKUUP..-XXPK			DKB..-XXPCK		
	20 (2.5 mm²)	P.135		80 (25 mm²)	P.139
				100 (50 mm²)	P.139
				150 (70 mm²)	P.139
				200 (95 mm²)	P.140
				300 (240 mm²)	P.140
				500 (300 mm²)	P.140
			DKBB..-XXPCK		
				10 (2.5 mm²)	P.137

Spring Connection Panel Type Terminal Blocks

Feed-through Single Wire Connection			Feed-through Double Wire Connection		
PM..WN-XXP			PMM..WN-XXP		
	2.5 mm²	P.144		2.5 mm²	P.144

Screw Connection Panel Type Terminal Blocks

Feed-through Terminal Blocks			Feed-through High-Voltage Terminal Blocks		
PM..N-XXP			PM..H-XXP		
	2.5 mm²	P.145		6 mm²	P.146
	4 mm²	P.145		16 mm²	P.146
	6 mm²	P.145			
	10 mm²	P.146			

Accessories


End Bracket	P.148	Fuse	P.155		
Marking Block	P.149	DIN Rail Cap	P.155		
Separating Disk	P.149	DIN Rail & DIN Rail Cutter	P.156		
Partition Plate	P.150	Marking System	P.157~P.163		
Reducing Bridge	P.151	Hands Tools	P.166		
Screw-on Bridge	P.152	Ferrules	P.167~P.168		
Cross Connection System	P.152~P.153				
Insertion Bridge	P.153~P.154				

Dinkle remains the right of product modification and engineering change of design. The catalogue is for reference only. The final product is made according to actual engineering drawing.

弊社標準品に関しては、修正や設計変更等が行われるため、カタログは参考であり、詳細仕様は図面を基準とする。
本公司对产品保有修改、设变权，目录仅供参考，实际产品仍需依照工程图面为准。

Push-In Design Terminal

- Push-In Design (PID) is a very popular wiring mechanism. This is accomplished with S-cage, a design that combines the concept of spring and wire cage for an efficient and reliable connection.
- The main characteristic of PID can be inserted by solid wires and stranded wires with ferrules easily without tools. The spring offers a high clamping force on the conductor, which provides a stable conductivity through every wired component.
- PID terminal blocks have the same reliable connection like the conventional screw type, but with a more efficient installation method, that results in time and labor cost saving during field wiring.
- Dinkle's PID product series is definitely worthy of your trust and application.



Feed-through Grounding Terminal Blocks



The PID, DP..N-PE series allows solid conductor direct insertion without tool for quick connection.

High quality conducting material for low connection resistance and high conducting performance.

Suitable for wire sizes from 1.5mm² to 16mm² the accessories are available for marking and bridging.

DP..-PE

Accessories

End cover

Partition plate

Plug-in bridge

2

3

4

5

10

20

Test plug

Spacer

Marking block


Marking label (Center / Outer)

Continuous flat marking label (Center / Outer)

DIN rail


Tool (mm)

Ferrule




DP1.5N-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	300	500
Rated Current	(A)		
Rated impulse voltage			6KV
Wire range (AWG/mm ²)		26~14	0.14~1.5
Connection Capacity			
Max. Solid (mm ²)			1.5
Max. Stranded (mm ²)			1.5
General Data			
Stripping length	(mm)	8	
Insulation material		PA	
T / W	(mm)	3.5 / 47.2	
H / H on TS-35	(mm)	30.6 / 32	
Package		100	

Part number	Package
DP1.5C-GN	50
AKSPS-001	50
DSD03-1.502	50
DSD03-1.503	50
DSD03-1.504	50
DSD03-1.505	10
DSD03-1.510	10
DSD03-1.520	10
0208-T004	
0208-E004	
MKG-001 / MKG-002	200
TM46W / TM41W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
0.4 x 2.5 DNT11-0102	
Page 166~167	



DP2.5N-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	800
Rated Current	(A)		
Rated impulse voltage			8KV
Wire range (AWG/mm ²)		26~12	0.14~2.5
Connection Capacity			
Max. Solid (mm ²)			4
Max. Stranded (mm ²)			2.5
General Data			
Stripping length	(mm)	10	
Insulation material		PA	
T / W	(mm)	5.1 / 49	
H / H on TS-35	(mm)	35 / 36.5	
Package		100	


Part number	Package
DP2.5C-GN	50
AKSPS-001	50
DSD01-2.502N	50
DSD01-2.503N	50
DSD01-2.504N	50
DSD01-2.505N	10
DSD01-2.510N	10
DSD01-2.520N	10
0208-T001	
0208-E001	
MKG-003 / MKG-004	200
TM47W / TM42W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
0.6 x 3.5 DNT11-0107	
Page 166~167	



DP4N-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	800
Rated Current	(A)		
Rated impulse voltage			8KV
Wire range (AWG/mm ²)		24~10	0.2~4
Connection Capacity			
Max. Solid (mm ²)			6
Max. Stranded (mm ²)			4
General Data			
Stripping length	(mm)		12
Insulation material			PA
T / W	(mm)		6.1 / 57
H / H on TS-35	(mm)		35 / 36.5
Package			100


Part number	Package
DP4C-GN	50
AKSPS-001	50
DSD01-402N	50
DSD01-403N	50
DSD01-404N	50
DSD01-405N	10
DSD01-410N	10
DSD01-420N	10
0208-T002	
0208-E002	
MKG-003 / MKG-004	200
TM48W / TM43W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
0.8 x 4 DNT11-0109	
Page 166~167	

Feed-through Grounding Terminal Blocks




DP6N-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	1000
Rated Current	(A)		
Rated impulse voltage			8KV
Wire range (AWG/mm ²)		20-8	0.5-6
Connection Capacity			
Max. Solid (mm ²)			10
Max. Stranded (mm ²)			6
General Data			
Stripping length (mm)			12
Insulation material			PA
T / W (mm)			8 / 57.8
H / H on TS-35			42.0 / 43.5
Package			50

Part number	Package
DP6C-GN	50
AKSPS-002	50
DSD01-602N	50
DSD01-603N	50
DSD01-604N	50
DSD01-605N	10
DSD01-610N	10
0208-T003	
0208-E003	
TM49W / TM44W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
0.8 x 4 DNT11-0109	
Page 166~167	




DP10-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	1000
Rated Current	(A)		
Rated impulse voltage			8KV
Wire range (AWG/mm ²)		20~6	0.5~10
Connection Capacity			
Max. Solid (mm ²)			16
Max. Stranded (mm ²)			10
General Data			
Stripping length (mm)			18
Insulation material			PA
T / W (mm)		10 / 69	
H / H on TS-35		49.3 / 50.1	
Package			50

Part number	Package
DP10C-GN	50
DSD01-1002N	50
DSD01-1003N	50
DSD01-1004N	50
DSD01-1005N	10
TM50W / TM45W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
1.0 x 5.5 DNT11-0111	
Page 166~167	



DP16-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	1000
Rated Current	(A)		
Rated impulse voltage			8KV
Wire range (AWG/mm ²)		20~4	0.5~16
Connection Capacity			
Max. Solid (mm ²)			25
Max. Stranded (mm ²)			16
General Data			
Stripping length (mm)			18
Insulation material			PA
T / W (mm)		12 / 76.5	
H / H on TS-35		53.1 / 54.3	
Package			50

Part number	Package
DP16C-GN	50
DSD01-1602N	50
TM50W / TM45W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
1.0 x 5.5 DNT11-0111	
Page 166~167	



Rated Data		UL	IEC
Rated Voltage	(V)		
Rated Current	(A)		
Rated impulse voltage			
Wire range (AWG/mm²)			
Connection Capacity			
Max. Solid (mm²)			
Max. Stranded (mm²)			
General Data			
Stripping length	(mm)		
Insulation material			
T / W	(mm)		
H / H on TS-35			
Package			

Push-In Design

Feed-through 3-Conductor Grounding Terminal Blocks




The PID, DP..N-TN-PE series is a 3 port grounding terminal block with the same dimensions as the PID, DP...N-TN series, and fully compliant to IEC 60947-7-2. This series supports both the mechanical and the electrical functions of a PCTB by using it as a ground (PE) busbar.

DP..TN-PE


Accessories

- End cover
- Partition plate
- Plug-in bridge
- 2
- 3
- 4
- 5
- 10
- 20
- Test plug
- Spacer
- Marking block
- Marking label (Center / Outer)
- Continuous flat marking label (Center / Outer)
- DIN rail
- Tool (mm)
- Ferrule




DP1.5N-TN-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	300	500
Rated Current	(A)		
Rated impulse voltage			6KV
Wire range (AWG/mm²)		26~14	0.14~1.5
Connection Capacity			
Max. Solid	(mm²)		1.5
Max. Stranded	(mm²)		1.5
General Data			
Stripping length	(mm)		8
Insulation material			PA
T / W	(mm)		3.5 / 58.7
H / H on TS-35	(mm)		30.6 / 32.1
Package			100

Part number	Package
DP1.5C-TN-GN	50
AKSPS-003	50
DSD03-1.502	50
DSD03-1.503	50
DSD03-1.504	50
DSD03-1.505	10
DSD03-1.510	10
DSD03-1.520	10
0208-T004	
0208-E004	
MKG-001 / MKG-002	200
TM46W / TM41W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
0.4 x 2.5 DNT11-0102	
Page 166~167	



DP2.5N-TN-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	800
Rated Current	(A)		
Rated impulse voltage			8KV
Wire range (AWG/mm²)		26~12	0.14~2.5
Connection Capacity			
Max. Solid	(mm²)		4
Max. Stranded	(mm²)		2.5
General Data			
Stripping length	(mm)		10
Insulation material			PA
T / W	(mm)		5.1 / 60.8
H / H on TS-35	(mm)		35 / 36.5
Package			100


Part number	Package
DP2.5C-TN-GN	50
AKSPS-003	50
DSD01-2.502N	50
DSD01-2.503N	50
DSD01-2.504N	50
DSD01-2.505N	10
DSD01-2.510N	10
DSD01-2.520N	10
0208-T001	
0208-E001	
MKG-003 / MKG-004	200
TM47W / TM42W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
0.6 x 3.5 DNT11-0107	
Page 166~167	



DP4N-TN-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	800
Rated Current	(A)		
Rated impulse voltage			8KV
Wire range (AWG/mm²)		24~10	0.2~4
Connection Capacity			
Max. Solid	(mm²)		6
Max. Stranded	(mm²)		4
General Data			
Stripping length	(mm)		12
Insulation material			PA
T / W	(mm)		6.1 / 67.3
H / H on TS-35	(mm)		35 / 36.5
Package			50


Part number	Package
DP4C-TN-GN	50
AKSPS-003	50
DSD01-402N	50
DSD01-403N	50
DSD01-404N	50
DSD01-405N	10
DSD01-410N	10
DSD01-420N	10
0208-T002	
0208-E002	
MKG-003 / MKG-004	200
TM48W / TM43W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
0.8 x 4 DNT11-0109	
Page 166~167	

Feed-through 3-Conductor Grounding Terminal Blocks



DP6N-TN-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	1000
Rated Current	(A)		
Rated impulse voltage			8KV
Wire range (AWG/mm²)		20~8	0.5~6
Connection Capacity			
Max. Solid	(mm²)		10
Max. Stranded	(mm²)		6
General Data			
Stripping length	(mm)		12
Insulation material			PA
T / W	(mm)		8 / 74.6
H / H on TS-35	(mm)		42 / 43.5
Package			50

Part number	Package
DP6C-TN-GN	50
AKSPS-003	50
DSD01-602N	50
DSD01-603N	50
DSD01-604N	50
DSD01-605N	10
DSD01-610N	10
0208-T003	
0208-E003	
TM49W / TM44W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
0.8 x 4 DNT11-0109	
Page 166~167	




DP10-TN-PE			
Rated Data		UL	IEC
Rated Voltage		600	1000
Rated Current			
Rated impulse voltage			8KV
Wire range (AWG/mm²)		20~6	0.5~10
Connection Capacity			
Max. Solid	(mm²)		16
Max. Stranded	(mm²)		10
General Data			
Stripping length	(mm)		18
Insulation material			PA
T / W	(mm)		10 / 90.5
H / H on TS-35	(mm)		49.3 / 50.1
Package			50

Part number	Package
DP10C-TN-GN	50
DSD01-1002N	50
DSD01-1003N	50
DSD01-1004N	50
DSD01-1005N	10
TM50W / TM45W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
1.0 x 5.5 DNT11-0111	
Page 166~167	



DP10C-TN-GN			
Rated Data		UL	IEC
Rated Voltage			
Rated Current			
Rated impulse voltage			
Wire range (AWG/mm²)			
Connection Capacity			
Max. Solid	(mm²)		
Max. Stranded	(mm²)		
General Data			
Stripping length	(mm)		
Insulation material			
T / W	(mm)		
H / H on TS-35	(mm)		
Package			

Part number	Package
DP10C-TN-GN	50
DSD01-1002N	50
DSD01-1003N	50
DSD01-1004N	50
DSD01-1005N	10
TM50W / TM45W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
1.0 x 5.5 DNT11-0111	
Page 166~167	



DP10C-TN-GN			
Rated Data		UL	IEC
Rated Voltage			
Rated Current			
Rated impulse voltage			
Wire range (AWG/mm²)			
Connection Capacity			
Max. Solid	(mm²)		
Max. Stranded	(mm²)		
General Data			
Stripping length	(mm)		
Insulation material			
T / W	(mm)		
H / H on TS-35	(mm)		
Package			


Part number	Package
DP10C-TN-GN	50
DSD01-1002N	50
DSD01-1003N	50
DSD01-1004N	50
DSD01-1005N	10
TM50W / TM45W	10
TM-R200 / TM-R100	10
TS-35	20
TS-35/15	10
1.0 x 5.5 DNT11-0111	
Page 166~167	

Potential distribution Terminal Blocks Introduction


DKD and DPD series provide multi-point potential distribution, which can be used in power cord management and configuration.

The input terminal of DKD series adopts screw-type wiring structure. The screw connection structure is vibration-resistant, anti-loosening, and features of a large contact area, which is more stable in power transmission. The output terminal adopts PID structure, which can be wired by solid wire or ferruled wire directly without tools. PID connection structure can quickly connect wires and greatly reduce the wiring time.

Both input and output terminals of DPD series are PID structure, which makes DPD series be wired easily and operated conveniently. The DPD6 of this series features of a high-density multi-layer design, which can be used in limited spaces.



The input terminals of DKD35, DPD10 and DPD16 series provide current from 60A to 120A, which output terminals provides 4 to 12 connection points to meet the needs of various potential distributions. In addition, these series offer in different colors to distinguish the application.



The connection number is originally 28 points, which can be expanded to more than 80 points by using the insertion bridges. In addition, red and blue terminal blocks are available to intuitively identify the positive and negative electricity and reduce the errors of manual wiring.



Both DKD & DPD series are able to be equipped with continuous flat marking labels in different colors which are easy to install and make the terminal block clear and identifiable. The marking system makes terminal blocks easier to identify and install, save the operation time when wiring.

Potential distribution Terminal Blocks




The DPD6-P series are designed for multi-potential distribution. The products support 28 contact points enables a space-saving potential distribution. Equipotential can be established by jumper bars.

DPD..P..

Accessories

End cover	
Plug-in bridge	
Continuous flat marking label	
DIN rail	
Tool (mm)	
Ferrule	





DPD6-P001		
Input Rated Data	UL	IEC
Rated Voltage (V)	300	250
Rated Current (A)	25	32
Rated impulse voltage		4KV
Wire range (AWG/mm ²)	24~10	0.2~6
Stripping length (mm)	14~15	
Output Rated Data		
Rated Voltage (V)	300	250
Rated Current (A)	15	17.5
Rated impulse voltage		4KV
Wire range (AWG/mm ²)	26~14	0.14~2.5
Stripping length (mm)	10~11	
General Data		
Insulation material	PA	
T / W (mm)	8.3 / 100	
H / H on TS-35 (mm)	86 / 87.5	
Package	50	
Color	Part number	Package
■	DPD6-P001-RD	50
■	DPD6-P001-BL	50
Part number Package		
DPD6C		
DPD6C-38		
DPD6C-83		
DSD03-M1XXX		
TM-R200		
TS-35		
TS-35/15		
0.4 x 2.5 DNT11-0102		
0.8 x 4 DNT11-0109		
Page 166~167		



DPD6-P002		
Input Rated Data	UL	IEC
Rated Voltage (V)		
Rated Current (A)		
Rated impulse voltage		
Wire range (AWG/mm ²)		
Stripping length (mm)		
Output Rated Data		
Rated Voltage (V)	300	250
Rated Current (A)	15	17.5
Rated impulse voltage		4KV
Wire range (AWG/mm ²)	26~14	0.14~2.5
Stripping length (mm)	10~11	
General Data		
Insulation material	PA	
T / W (mm)	8.3 / 100	
H / H on TS-35 (mm)	86 / 87.5	
Package	50	
Color	Part number	Package
■	DPD6-P002-RD	50
■	DPD6-P002-BL	50
Part number Package		
DPD6C		
DPD6C-38		
DPD6C-83		
DSD03-M1XXX		
TM-R200		
TS-35		
TS-35/15		
0.4 x 2.5 DNT11-0102		
Page 166~167		



DPD6C		
Output Rated Data		
Rated Voltage (V)	300	250
Rated Current (A)	15	17.5
Rated impulse voltage		4KV
Wire range (AWG/mm ²)	26~14	0.14~2.5
Stripping length (mm)	10~11	
General Data		
Insulation material	PA	
T / W (mm)	8.3 / 100	
H / H on TS-35 (mm)	86 / 87.5	
Package	50	
Color	Part number	Package
■	DPD6C-38	50
■	DPD6C-83	50
Part number Package		
DSD03-M1XXX		
TM-R200		
TS-35		
TS-35/15		
0.4 x 2.5 DNT11-0102		
Page 166~167		



DSD03-M1XXX		
Length	Part Number	Package
50mm	DSD03-M1050	50
500mm	DSD03-M1500	10


Plug-in Connection Terminal Blocks



PID

DPES2.5 is a plug-in type terminal block that enables signal transmission and power feeding function. The anti-vibration insertion force allows the plug to be firmly connected onto the terminal base. Current can be inputted from both the base and the plug. It is equipped with a series of accessories such as plug, strain relief, latch and marking labels.


DPES2.5



DPES2.5			
Rated Data		UL	IEC
Rated Voltage	(V)	600	800
Rated Current	(A)	20	24
Rated impulse voltage		6KV	
Wire range (AWG/mm²)		26~12	0.14~2.5
Connection Capacity			
Max. Solid (mm²)		4	
Max. Stranded (mm²)		2.5	
General Data			
Stripping length (mm)		10	
Insulation material		PA	
T / W (mm)		5.08 / 51	
H / H on TS-35		35 / 36.5	
Package		100	
Color	Part number	Package	



DPES2.5-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	600	800
Rated Current	(A)		
Rated impulse voltage		6KV	
Wire range (AWG/mm²)		26~12	0.14~2.5
Connection Capacity			
Max. Solid (mm²)		4	
Max. Stranded (mm²)		2.5	
General Data			
Stripping length (mm)		10	
Insulation material		PA	
T / W (mm)		5.08 / 51	
H / H on TS-35		35 / 36.5	
Package		100	
Color	Part number	Package	



DP2.5PG-XXP			
Rated Data		UL	IEC
Rated Voltage	(V)	600	800
Rated Current	(A)	20	24
Rated impulse voltage		8KV	
Wire range	(AWG/mm ²)	26~12	0.14~2.5
Connection Capacity			
Max. Solid (mm ²)		4	
Max. Stranded (mm ²)		2.5	
General Data			
Stripping length (mm)		10	
Insulation material		PA	
T / W (mm)		-	
H / H on TS-35		-	
Package		-	
Color	Part number	Package	

DP2.5PG-XXP-WPE	50
Part number	Package

Accessories

End cover	
Plug-in bridge	
2	
3	
4	
5	
10	
20	
Test plug	
Spacer	
Marking label (Center / Outer)	
Continuous flat marking label (Center / Outer)	
DIN rail	
Strain relief	
Latch	
Tool (mm)	
Ferrule	

Part number	Package
DPES2.5C	50
DSD01-2.502N	50
DSD01-2.503N	50
DSD01-2.504N	50
DSD01-2.505N	10
DSD01-2.510N	10
DSD01-2.520N	10
0208-T001	
0208-E001	
TM42W / TM47W	10
TM-R100 / TM-R200	10
TS-35	20
TS-35/15	10
DP-PZ-02P	50
DP-PZ-04P	50
DP-PR	50
0.6 x 3.5 DNT11-0107	
Page 166~167	

Part number	Package
DPES2.5C-GN	50
DSD01-2.502N	50
DSD01-2.503N	50
DSD01-2.504N	50
DSD01-2.505N	10
DSD01-2.510N	10
DSD01-2.520N	10
0208-T001	
0208-E001	
TM42W / TM47W	10
TM-R100 / TM-R200	10
TS-35	20
TS-35/15	10
DP-PZ-02P	50
DP-PZ-04P	50
DP-PR	50
0.6 x 3.5 DNT11-0107	
Page 166~167	

Part number	Package
TM42W	10
TM-R100	10
DP-PZ-02P	50
DP-PZ-04P	50
DP-PR	50
0.6 x 3.5 DNT11-0107	
Page 166~167	


DP2.5/4 Knife and Disconnect Terminal Blocks Introduction



The blades AKP-TP and AKP-TG are able to connect and disconnect quickly. The component carrier AKP-CP adopts diodes, resistors or other electronic components required for circuit solution.

Upper layer of the compact double layers design support knife and disconnect function, lower layer support grounding.

Marking system by continuous label strip offer clear marking identification and easy installation.



Blade disconnecting terminal block supports AKP-TP, AKP-TG, AKP-CP blades. Fast circuit disconnection can be established through AKP-TP and AKP-TG. The component carrier AKP-CP adopts resistor, diode and other electronic components required for circuit solution.

PID terminal blocks offer compact wiring connection in constrained space. Additionally, the product supports double level with variety structure of blade on the upper level while the second level applies to grounding, which increase space utility of the device.

The product has 2 jumper slots, which enables any numbers of terminal blocks to be shorted by use of 2P jumper. Mating with the continuous flat marking label makes easy and clear indication for installation and makes wiring much efficient.

Strain relief



02P DP-PZ-02P
04P DP-PZ-04P


Latch



DP-PR

Pole	Part Number	Package
2	DP2.5PG-02P	100
3	DP2.5PG-03P	100
4	DP2.5PG-04P	100
5	DP2.5PG-05P	50
6	DP2.5PG-06P	50
7	DP2.5PG-07P	50
8	DP2.5PG-08P	50

Bi-Level Knife and Disconnect Terminal Blocks




The PID, DPP2.5N-T is the double level knife disconnect terminal block, are characterized by its compact structure and easy disconnection of the circuit for testing. The product has two individual potentials for higher density contact, and supports plug-in bridge for equipotential function.


DPP2.5N-..

Accessories


- End cover
- Plug-in bridge
- 2
- 3
- 4
- 5
- 10
- 20
- Test plug
- Spacer
- Marking label
- Continuous flat marking label
- DIN rail
- Tool (mm)
- Ferrule



DPP2.5N-TP			
Rated Data		UL	IEC
Rated Voltage	(V)	300	400
Rated Current	(A)	18/20	20
Rated impulse voltage		6KV	
Wire range (AWG/mm²)		26~12	0.2~2.5
Connection Capacity			
Max. Solid	(mm²)	4	
Max. Stranded	(mm²)	2.5	
General Data			
Stripping length	(mm)	10	
Insulation material		PA	
T / W	(mm)	5.1 / 78.5	
H / H on TS-35	(mm)	60.1 / 61.6	
Package		100	
Color	Part number	Package	
■	DPP2.5N-TP-RD	100	
■	DPP2.5N-TP-BL	100	
	Part number	Package	
	DPP2.5C-T	50	
	DSD01-2.502N	50	
	DSD01-2.503N	50	
	DSD01-2.504N	50	
	DSD01-2.505N	10	
	DSD01-2.510N	10	
	DSD01-2.520N	10	
	0208-T001		
	0208-E001		
	TM42W	10	
	TM-R100	10	
	TS-35	20	
	TS-35/15	10	
	0.6 x 3.5 DNT11-0107		
	Page 166~167		



DPP2.5N-TG			
Rated Data		UL	IEC
Rated Voltage	(V)	300	400
Rated Current	(A)	18/20	20
Rated impulse voltage		6KV	
Wire range (AWG/mm²)		26~12	0.2~2.5
Connection Capacity			
Max. Solid	(mm²)	4	
Max. Stranded	(mm²)	2.5	
General Data			
Stripping length	(mm)	10	
Insulation material		PA	
T / W	(mm)	5.1 / 78.5	
H / H on TS-35	(mm)	47.7 / 49.2	
Package		100	
Color	Part number	Package	
■	DPP2.5N-TG-RD	100	
■	DPP2.5N-TG-BL	100	
Part number		Package	
DPP2.5C-T		50	
DSD01-2.502N		50	
DSD01-2.503N		50	
DSD01-2.504N		50	
DSD01-2.505N		10	
DSD01-2.510N		10	
DSD01-2.520N		10	
0208-T001			
0208-E001			
TM42W		10	
TM-R100		10	
TS-35		20	
TS-35/15		10	
0.6 x 3.5 DNT11-0107			
Page 166~167			



DPP2.5N-CP			
Rated Data		UL	IEC
Rated Voltage	(V)	300	400
Rated Current	(A)	6/20	6/20
Rated impulse voltage		6KV	
Wire range (AWG/mm²)		26~12	0.2~2.5
Connection Capacity			
Max. Solid	(mm²)	4	
Max. Stranded	(mm²)	2.5	
General Data			
Stripping length	(mm)	10	
Insulation material		PA	
T / W	(mm)	5.1 / 78.5	
H / H on TS-35	(mm)	67.2 / 68.7	
Package		100	
Color	Part number	Package	
■	DPP2.5N-CP-RD	100	
■	DPP2.5N-CP-BL	100	
	Part number	Package	
	DPP2.5C-T	50	
	DSD01-2.502N	50	
	DSD01-2.503N	50	
	DSD01-2.504N	50	
	DSD01-2.505N	10	
	DSD01-2.510N	10	
	DSD01-2.520N	10	
	0208-T001		
	0208-E001		
	TM42W	10	
	TM-R100	10	
	TS-35	20	
	TS-35/15	10	
0.6 x 3.5 DNT11-0107			
Page 166~167			

DP2.5/4 Fuse Terminal Blocks Introduction



The fuse terminal block supports cartridge fuse and car fuse, which with a 2-way LED indicator to afford the use of different current directions.

The product adopts rotary lever or lever type fuse carrier to be applied in various fields. PID connection method enables quick wiring and saves user's wiring time. The compact design provides high density connection in limited space.

It can support continuous flat marking labels, and the flexible marking system offers convenient installation and brings users more conveniences when wiring.





The fuse terminal block supports cartridge fuse, car fuse and two-way LED indicator to identify current direction. The product adopts rotary lever or lever type fuse carrier.



The product has 2 jumper slots, which enables any numbers of terminal blocks to be shorted by use of 2P jumper. Mating with the continuous flat marking label makes easy and clear indication for installation and makes wiring much efficient.





PID type is able to install wire without tool and save much wiring time, and offer high density wiring connection in limited space.



DP4N-TFULXX		
Rated Data	UL	IEC
Rated Voltage (V)	300	400
Rated Current (A)	15	10
Rated impulse voltage		6KV
Wire range (AWG/mm ²)	24~10	0.2~4
Connection Capacity		
Max. Solid (mm ²)		6
Max. Stranded (mm ²)		4
General Data		
Stripping length (mm)		12
Insulation material		PA
T / W (mm)		6.1 / 57
H / H on TS-35 (mm)		35 / 36.5
Package		100
Part number		Package
DP4C-TFU		50
DSD01-402N		50
DSD01-403N		50
DSD01-404N		50
DSD01-405N		10
DSD01-410N		10
DSD01-420N		10
0208-T002		
0208-E002		
TM43W		10
TM-R100		10
TS-35		20
TS-35/15		10
0.8 x 4 DNT11-0109		
Page 166~167		

Part number	LED	Voltage
DP4N-TFUL12	with LED light	12V
DP4N-TFUL24	with LED light	24V
DP4N-TFUL48	with LED light	48V



DP4N-TFULXX(5X20)			
Rated Data		UL	IEC
Rated Voltage	(V)	300	400
Rated Current	(A)	6.3	6.3
Rated impulse voltage		6KV	
Wire range (AWG/mm ²)		24~10	0.2~4
Connection Capacity			
Max. Solid	(mm ²)	6	
Max. Stranded	(mm ²)	4	
General Data			
Stripping length (mm)		12	
Insulation material		PA	
T / W	(mm)	6.1 / 57	
H / H on TS-35	(mm)	79 / 80.5	
Package		50	
Part number		Package	
DP4C-TFU		50	
DSD01-402N		50	
DSD01-403N		50	
DSD01-404N		50	
DSD01-405N		10	
DSD01-410N		10	
DSD01-420N		10	
0208-T002			
0208-E002			
TM43W		10	
TM-R100		10	
TS-35		20	
TS-35/15		10	
0.8 x 4 DNT11-0109			
FUK1A-01		50	
FUK2A-01		50	
FUK6.3A-01		50	
Page 166~167			


Part number	LED	Voltage
DP4N-TFUL5(5X20)	with LED light	5V
DP4N-TFUL12(5X20)	with LED light	12V
DP4N-TFUL24(5X20)	with LED light	24V
DP4N-TFUL48(5X20)	with LED light	48V
DP4N-TFUL110(5X20)	with LED light	110V
DP4N-TFUL220(5X20)	with LED light	220V
DP4N-TFUL300(5X20)	with LED light	300V




Spring Clamp Connection Terminal Block



- The spring clamp connection terminal block provides instant wiring and is designed to fully comply with the safety standards of UL1059, IEC60947-7-1 and IEC60947-7-2. The quality of the product is consistent and provides stable wiring connection performance.
- Excellent conductor material and design makes electrical performance meet the requirements of low resistance and high conductivity.
- With Dinkle's excellent material selection and design capabilities, the application is robust and durable even in vibration environment.





Accessories

End cover








Marking block

Marking label (Center / Outer)

Continuous flat marking label
(Center / Outer)

DIN rail

Tool (mm)



AK Fuse/Knife and Disconnect Terminal Blocks Introduction



Disconnect terminal blocks perform an important function in applications of measurement, regulation and control systems in order to quickly detect fault points and check status under zero voltage conditions.

User-friendly disconnect knife with low contact resistance and high current-carrying capacity saves application space.



Three kinds of knife design available; AKP-TP and AKP-TG are able to connect and disconnect connection quickly. AKP-CP is able to be equipped with diodes, resistors or other components to meet requests from various circuit tests.



Fuse and disconnect terminal blocks support cartridge fuse and 5V~300V two-way LED indicator which is for different current direction identification.



With 2 bridging slots design, any numbers of terminal block can be connected to short-circuit and configuration through 2P plug-in bridge. Continuous flat marking label provides clear identification and offers easy installation.

Knife and Disconnect Terminal Blocks




AK2.5-T series is a design with a universal socket on the top, which facilitates the insertion of different kinds of isolation plug, feed-through connectors and component connectors to carry out the disconnect function.

A complete range of accessories is available for easy identification, grouping and plug-in bridge applications.

AK2.5..T


Accessories

End cover	
Partition plate	
Plug-in bridge	
2	
3	
4	
5	
10	
20	
Marking label (Center / Outer)	
Continuous flat marking label (Center / Outer)	
DIN rail	
Tool (mm)	




AK2.5-TP		
Rated Data	UL	IEC
Rated Voltage (V)	300	400
Rated Current (A)	16	21
Rated impulse voltage	6KV	
Wire range (AWG/mm ²)	28-12	0.2-2.5
Connection Capacity		
Max. Solid (mm ²)	2.5	
Max. Stranded (mm ²)	2.5	
General Data		
Stripping length (mm)	10	
Insulation material	PA	
T / W (mm)	5.1 / 60.8	
H / H on TS-35 (mm)	49.1 / 50.6	
Package	100	

Color	Part number	Package
■	AK2.5-TP-RD	100
■	AK2.5-TP-BL	100
Part number		
AK2.5C-TN		
AKSPS-003		
2 way	DSD01-2.502N	50
3 way	DSD01-2.503N	50
4 way	DSD01-2.504N	50
5 way	DSD01-2.505N	10
10 way	DSD01-2.510N	10
20 way	DSD01-2.520N	10
TM47W / TM42W		
TM-R200 / TM-R100		
TS-35		
TS-35/15		
0.6 x 3.5 DNT11-0107		



AK2.5-TG		
Rated Data	UL	IEC
Rated Voltage (V)	300	400
Rated Current (A)	16	21
Rated impulse voltage	6KV	
Wire range (AWG/mm ²)	28~12	0.2~2.5
Connection Capacity		
Max. Solid (mm ²)	2.5	
Max. Stranded (mm ²)	2.5	
General Data		
Stripping length (mm)	10	
Insulation material	PA	
T / W (mm)	5.1 / 60.8	
H / H on TS-35 (mm)	36.7 / 38.2	
Package	50	

Color	Part number	Package
■	AK2.5-TG-RD	50
■	AK2.5-TG-BL	50
Part number		
AK2.5C-TN		
AKSPS-003		
2 way	DSD01-2.502N	50
3 way	DSD01-2.503N	50
4 way	DSD01-2.504N	50
5 way	DSD01-2.505N	10
10 way	DSD01-2.510N	10
20 way	DSD01-2.520N	10
TM47W / TM42W		
TM-R200 / TM-R100		
TS-35		
TS-35/15		
0.6 x 3.5 DNT11-0107		




AK2.5-CP		
Rated Data	UL	IEC
Rated Voltage (V)	300	400
Rated Current (A)	6	6
Rated impulse voltage	6KV	
Wire range (AWG/mm ²)	28~12	0.2~2.5
Connection Capacity		
Max. Solid (mm ²)	4	
Max. Stranded (mm ²)	2.5	
General Data		
Stripping length (mm)	10	
Insulation material	PA	
T / W (mm)	5.1 / 60.8	
H / H on TS-35 (mm)	56.5 / 58	
Package	50	




Color	Part number	Package
■	AK2.5-CP-RD	50
■	AK2.5-CP-BL	50
Part number		
AK2.5C-TN		
AKSPS-003		
2 way	DSD01-2.502N	50
3 way	DSD01-2.503N	50
4 way	DSD01-2.504N	50
5 way	DSD01-2.505N	10
10 way	DSD01-2.510N	10
20 way	DSD01-2.520N	10
TM47W / TM42W		
TM-R200 / TM-R100		
TS-35		
TS-35/15		
0.6 x 3.5 DNT11-0107		

Screw Connection Terminal Block

- Potential power distribution can be arranged using various plug-in, insertion and screw-on bridges.
- IEC 60947-7-1 & UL 1059 compliance.



Feed-through Grounding Terminal Blocks



DK50-PE		
Rated Data	UL	IEC
Rated Voltage (V)	600	1000
Rated Current (A)		
Rated impulse voltage		8KV
Wire range (AWG/mm²)	6	16~50
Connection Capacity		
Max. Solid (mm²)		
Max. Stranded (mm²)		50
General Data		
Torque Wire (N.m)	7.9	
Torque Din Rail (N.m)	3.3	
Screw thread	M6	
Stripping length (mm)	20~25	
Insulation material	PA	
T / W (mm)	20 / 70.5	
H / H on TS-35 (mm)	75.6 / 76.6	
Package	10	
Part number	Package	
TM50W	10	
TM-R200	10	
TS-35	20	
TS-35/15	10	
5mm		

(Copper DIN rail installation)

DK95-PE		
Rated Data	UL	IEC
Rated Voltage (V)	600	1000
Rated Current (A)		
Rated impulse voltage		8KV
Wire range (AWG/mm²)	2~4/0	35~95
Connection Capacity		
Max. Solid (mm²)		
Max. Stranded (mm²)		95
General Data		
Torque Wire (N.m)	17.9	
Torque Din Rail (N.m)	5.6	
Screw thread	M8	
Stripping length (mm)	20~25	
Insulation material	PA	
T / W (mm)	25 / 80	
H / H on TS-35 (mm)	86.1 / 89.9	
Package	10	
Part number	Package	
TM50W	10	
TM-R200	10	
TS-35	20	
TS-35/15	10	
6mm		

(Copper DIN rail installation)

DK...- PE is a protective conductor terminal block, fully compliant with all the strict requirements of UL 1059 and IEC 60947-7-2. The DIN rail is not only a mechanical support to the PCTB but also an electrical function of the PCTB, it is used as a ground (PE) busbar.

Ensure secured wiring, High conductivity and low resistance for safe grounding. Additional to the snap-on foot, with screw mounting to strengthen the fix on the DIN rail.

DK...-PE

Accessories

Marking label





Continuous flat marking label

DIN rail

Tool (mm)

DK2.5-PE		
Rated Data	UL	IEC
Rated Voltage (V)	600	630
Rated Current (A)		
Rated impulse voltage		8KV
Wire range (AWG/mm²)	26~12	0.5~2.5
Connection Capacity		
Max. Solid (mm²)		4
Max. Stranded (mm²)		2.5
General Data		
Torque Wire (N.m)	0.8	
Torque Din Rail (N.m)	0.52	
Screw thread	M3	
Stripping length (mm)	10~14	
Insulation material	PA	
T / W (mm)	5.7 / 56	
H / H on TS-35 (mm)	46.4 / 47.4	
Package	100	
Part number	Package	
TM47W	10	
TM-R200	10	
TS-35	20	
TS-35/15	10	
0.6 x 3.5 DNT11-0107		

Feed-through Grounding Terminal Blocks



DK4-PE		
Rated Data	UL	IEC
Rated Voltage (V)	600	630
Rated Current (A)		
Rated impulse voltage		8KV
Wire range (AWG/mm²)	26~10	0.5~4
Connection Capacity		
Max. Solid (mm²)		6
Max. Stranded (mm²)		4
General Data		
Torque Wire (N.m)	0.8	
Torque Din Rail (N.m)	0.52	
Screw thread	M3	
Stripping length (mm)	12~16	
Insulation material	PA	
T / W (mm)	6.6 / 56	
H / H on TS-35 (mm)	46.4 / 47.4	
Package	100	
Part number	Package	
TM48W	10	
TM-R200	10	
TS-35	20	
TS-35/15	10	
0.6 x 3.5 DNT11-0107		

DK10-PE		
Rated Data	UL	IEC
Rated Voltage (V)	600	500
Rated Current (A)		
Rated impulse voltage		8KV
Wire range (AWG/mm²)	16~8	1.5~10
Connection Capacity		
Max. Solid (mm²)		16
Max. Stranded (mm²)		10
General Data		
Torque Wire (N.m)	1.76	
Torque Din Rail (N.m)	0.8	
Screw thread	M4	
Stripping length (mm)	12~16	
Insulation material	PA	
T / W (mm)	10.4 / 56	
H / H on TS-35 (mm)	46.4 / 47.4	
Package	50	
Part number	Package	
TM50W	10	
TM-R200	10	
TS-35	20	
TS-35/15	10	
0.8 x 4 DNT11-0109		

DK16-PE		
Rated Data	UL	IEC
Rated Voltage (V)	600	1000
Rated Current (A)		
Rated impulse voltage		8KV
Wire range (AWG/mm²)	14~6	2.5~16
Connection Capacity		
Max. Solid (mm²)		25
Max. Stranded (mm²)		16
General Data		
Torque Wire (N.m)	3.4	
Torque Din Rail (N.m)	0.8	
Screw thread	M5	
Stripping length (mm)	14~18	
Insulation material	PA	
T / W (mm)	12 / 56	
H / H on TS-35 (mm)	62.4 / 63.4	
Package	20	
Part number	Package	
TM50W	10	
TM-R200	10	
TS-35	20	
TS-35/15	10	
1.0 x 5.5 DNT11-0111		

Rated Data	UL	IEC
Rated Voltage (V)		
Rated Current (A)		
Rated impulse voltage		
Wire range (AWG/mm²)		
Connection Capacity		
Max. Solid (mm²)		
Max. Stranded (mm²)		
General Data		
Torque Wire (N.m)		
Torque Din Rail (N.m)		
Screw thread		
Stripping length (mm)		
Insulation material		
T / W (mm)		
H / H on TS-35 (mm)		
Package		
Part number	Package	

Screw Connection

DK Sensor/Actuator Terminal Blocks Introduction



DK1.5SG series supports the connection with 3-wire sensors. The user performs the wiring of the NPN and/or PNP according to the required conditions.

Cross connection bridges are available, with which DK1.5SG can connect the positive and negative electrodes to the same potential. DK1.5SGF-PE can further support grounding function.

The screw connection method makes stable electrical connection in the application of signal and power transmission. In addition, it can also equip with continuous flat marking labels and bridges in different colors, and using the excellent marking system to make the wiring identification more convenient.




Advantages of screw connection:

- 1. Vibration resistance
- 2. Anti-loosening
- 3. Stable transmission




It can connect with various sensors to perform control process. DK1.5SGF mating with bridges can distribute the potential to various sensors. In addition, DK1.5SGF-PE also provides a grounding point for completion of sensor's ground-wiring.



Equipped with a continuous flat marking label, the terminal block can be identified clearly and make the installation convenient. Besides, the continuous flat marking label in different colors to identify the potentials easily when wiring.

Sensor / Actuator Terminal Blocks




DK1.5SG.. is a sensor/actuator terminal block in 3 layers. The top layer supports signal lines, and the second and/or third layers support positive and negative potentials.

In addition, the third layer also supports insertion bridges to establish equipotential.


DK1.5SG..

Accessories


End cover	
Plug-in bridge	
Marking label	
Continuous flat marking label	
DIN rail	
Tool (mm)	



DK1.5SG DK1.5SG-LXX *			
Rated Data		UL	IEC
Rated Voltage	(V)	300	250
Rated Current	(A)	15	17.5
Rated impulse voltage		4KV	
Wire range	(AWG/mm ²)	24~14	0.2~1.5
Connection Capacity			
Max. Solid	(mm ²)	2.5	
Max. Stranded	(mm ²)	2.5	
General Data			
Torque	(N.m)	0.4~0.45	
Screw thread		M2.5	
Stripping length		(mm) 8~9	
Insulation material		PA	
T / W	(mm)	5.1 / 60.4	
H / H on TS-35	(mm)	50.7 / 52.0	
Package		50	
Part number		Package	
DK1.5SGC		50	
DSD02-1.580		20	
TM42W		10	
TM-R100		10	
TS-35		20	
TS-35/15		10	
0.4 x 2.5 DNT11-0102			





DK1.5SGF			
Rated Data		UL	IEC
Rated Voltage	(V)	300	250
Rated Current	(A)	15	17.5
Rated impulse voltage		4KV	
Wire range	(AWG/mm²)	24~14	0.2~1.5
Connection Capacity			
Max. Solid	(mm²)	2.5	
Max. Stranded	(mm²)	2.5	
General Data			
Torque	(N.m)	0.4~0.45	
Screw thread		M2.5	
Stripping length		(mm) 8~9	
Insulation material		PA	
T / W	(mm)	6.1 / 60.4	
H / H on TS-35	(mm)	50.7 / 52.0	
Package		50	
Part number		Package	
DSD02-1.580		20	
TM42W		10	
TM-R100		10	
TS-35		20	
TS-35/15		10	
0.4 x 2.5 DNT11-0102			




DK1.5SGF-PE			
Rated Data		UL	IEC
Rated Voltage	(V)	300	250
Rated Current	(A)		
Rated impulse voltage			4KV
Wire range (AWG/mm²)		24~14	0.2~1.5
Connection Capacity			
Max. Solid	(mm)		2.5
Max. Stranded	(mm)		2.5
General Data			
Torque	(N.m)	0.4~0.45	
Screw thread		M2.5	
Stripping length	(mm)	8~9	
Insulation material		PA	
T / W	(mm)	6.1 / 60.4	
H / H on TS-35	(mm)	50.7 / 52.0	
Package		50	
Part number		Package	
DSD02-1.580		20	
TM42W		10	
TM-R100		10	
TS-35		20	
TS-35/15		10	
0.4 x 2.5 DNT11-0102			

*DK1.5SG-LXX with LED display.

Part number	LED	Voltage
DK1.5SG-L24	with LED light	24V



Can be cut to required length.



No of pole : 80

Part number	Color
DSD02-1.580	Black
DSD02-1.580-GN	Green
DSD02-1.580-RD	Red
DSD02-1.580-BL	Blue

Plug-in Connection Terminal Blocks



Modular terminal blocks with sockets on one side are demanded frequently in control system. DKES1.5 series are equipped with two sockets, one vertical entry on top and one horizontal entry on the side, various plugs for options. Accessories include protection covers, insertion bridges and marking labels. The multi-position cover can be divided in any pole numbers and snapped into the housing as shock protection for the contact pins when removing the plugs.

DKES1.5..

Accessories

End cover (left)

End cover (right)

Cover

Screw-on bridge

2

3

4

5

10

Marking label

Continuous flat marking label

DIN rail

Tool (mm)




DKES1.5		
Rated Data	UL	IEC
Rated Voltage (V)	300	250
Rated Current (A)	20	24
Rated impulse voltage		4KV
Wire range (AWG/mm²)	22~12	0.5~1.5
Connection Capacity		
Max. Solid (mm²)		1.5
Max. Stranded (mm²)		1.5
General Data		
Torque (N.m)	0.5	
Screw thread	M3	
Stripping length (mm)	9~10	
Insulation material	PA	
T / W (mm)	5.08 / 50.6	
H / H on TS-35 (mm)	42.4 / 43.5	
Color	Part number	Package
	DKES1.5	100

Part number	Package
DKES1.5CA / DKES1.5MCA	50
DKES1.5CB / DKES1.5MCB	50
DKESP1.5-XXP	50
DS2.5-02P	50
DS2.5-03P	50
DS2.5-04P	50
DS2.5-08P	10
DS2.5-10P	10
TM47W	10
TM-R200	10
TS-35	20
TS-35/15	10
0.6 x 3.5 DNT11-0107	



DKES1.5-XXP		
Rated Data	UL	IEC
Rated Voltage (V)	300	250
Rated Current (A)	20	24
Rated impulse voltage		4KV
Wire range (AWG/mm²)	22~12	0.5~1.5
Connection Capacity		
Max. Solid (mm²)		1.5
Max. Stranded (mm²)		1.5
General Data		
Torque (N.m)	0.5	
Screw thread	M3	
Stripping length (mm)	9~10	
Insulation material	PA	
T / W (mm)	5.08 / 50.6	
H / H on TS-35 (mm)	42.4 / 43.5	
Color	Part number	Package
	DKES1.5-01P	100
	DKES1.5-02P~06P	50
	DKES1.5-07P~10P	20

Part number	Package
DKESP1.5-XXP	50
DS2.5-02P	50
DS2.5-03P	50
DS2.5-04P	50
DS2.5-08P	10
DS2.5-10P	10
TM47W	10
TM-R200	10
TS-35	20
TS-35/15	10
0.6 x 3.5 DNT11-0107	



DKES1.5M-XXP		
Rated Data	UL	IEC
Rated Voltage (V)	300	250
Rated Current (A)	20	24
Rated impulse voltage		4KV
Wire range (AWG/mm²)	22~12	0.5~1.5
Connection Capacity		
Max. Solid (mm²)		1.5
Max. Stranded (mm²)		1.5
General Data		
Torque (N.m)	0.5	
Screw thread	M3	
Stripping length (mm)	9~10	
Insulation material	PA	
T / W (mm)	5.08 / 50.6	
H / H on TS-35 (mm)	42.4 / 43.5	
Color	Part number	Package
	DKES1.5M-01P	100
	DKES1.5M-02P~06P	50
	DKES1.5M-07P~10P	20


Part number	Package
DKESP1.5-XXP	50
DS2.5-02P	50
DS2.5-03P	50
DS2.5-04P	50
DS2.5-08P	10
DS2.5-10P	10
TM47W	10
TM-R200	10
TS-35	20
TS-35/15	10
0.6 x 3.5 DNT11-0107	

DK Knife and Disconnect Terminal Blocks Introduction

The fuse type terminal block supports glass cartridge fuse and 2-way LED indicator in application. Besides, the double-layer terminal block structure greatly increases the efficiency of space applications.

The knife type terminal block can be quickly disconnected and connected by AKP-TP and AKP-TG. With AKP-CP, it can support resistors, diodes and other electronic components application.


The screw connection method makes stable electrical connection in the application of signal and power transmission. In addition, it can also equip with continuous flat marking labels and bridges in different colors, and using the excellent marking system to make the wiring identification more convenient.



The blade comes with insulator to prevent electrical shot. The fuse-type terminal block supports cartridge fuse, as well as 5V~300V LED indicators. Double-layer design, the upper level supports cartridge fuse, and the lower layer provides grounding function.



The AKP-TP and AKP-TG can be applied for quick disconnection. The AKP-CP is the carrier of electronic components supporting resistors, diodes and other electronic components to support various requirement for circuit testing.




Equipped with a continuous flat marking label, the terminal block can be identified clearly and make the installation convenient. Besides, the continuous flat marking label in different colors to identify the potentials easily when wiring.

Mating Plugs




2ESV	2ESDV	2ESV	2ESDV	2ESV	2ESDV
Pole#	P/N	Pole#	P/N	Pole#	P/N
2	2ESV-02P	2	2ESDV-02P	2	2ESV-02P
3	2ESV-03P	3	2ESDV-03P	3	2ESV-03P
4	2ESV-04P	4	2ESDV-04P	4	2ESV-04P
8	2ESV-08P	8	2ESDV-08P	8	2ESV-08P
10	2ESV-10P	10	2ESDV-10P	10	2ESV-10P

A diagram showing a bolted joint. A bolt is inserted through a plate, and a lock washer is placed between the plate and the lock nut. The lock nut is tightened onto the bolt, and the lock washer is deformed to lock the nut in place.



© 2006 The Authors
Journal compilation © 2006 Blackwell Publishing Ltd

- End cover
- Plug-in bridge
 - 2
 - 3
 - 4
 - 5
 - 10
- Marking label
- Continuous flat marking label
- DIN rail
- Tool (mm)





Memo

Feed-Through Panel Type Terminal Blocks




- Suitable for the application in the lower power spectrum to connect to small motors.
- PM..N series are available to apply in power distribution in various position combination.
- Compact design applies in constrained space.
- Accessories including marking labels, bridges, and partition plates, that can meet various requirements.

Terminal Block

Panel Type Terminal Blocks

Introduction



For the application in the lower power spectrum to connect to small motors.

Apply in power distribution in various position combination.


Compact design applies in constrained space.



Easy-latching flange design on both sides offers firm and user-friendly connection to make locking and unlocking more easy.




Available in spring clamp and screw types, offer firm and durable connection even in vibrating applications. It meets requests from signal and power transmission.



Compact design offers high density wiring connection in constrained space. Available in 8A~76A to meet requests from various applications.

Spring Connection Panel Type Terminal Blocks



Suitable for the application in the lower power spectrum to connect to small motors.

PM(M)2.5WN series are available to apply in power distribution with 2& 4 wirings for options.

Compact design of Spring clamp design for anti-vibration. Available accessories include insertion bridges and marking labels.

PM..WN

Accessories


End cover (left)	
End cover (right)	
Marking label	
Tool (mm)	







PM2.5WN-XXP		
Rated Data	UL	IEC
Rated Voltage (V)	600	800
Rated Current (A)	20	24
Rated impulse voltage	8KV	
Wire range (AWG/mm²)	28~12	0.5~2.5
Connection Capacity		
Max. Solid (mm²)	4	
Max. Stranded (mm²)	2.5	
General Data		
Torque (N.m)		
Screws		
Stripping length (mm)	8~10	
Insulation material	PA	
T x H x W (mm)	5.1 x 22 x 32	
Package	50	
Color	Part number	Package
■	PM2.5WN-02P...12P-RD	50
■	PM2.5WN-02P...12P-BL	50
■	PM2.5WN-02P...12P-YG	50
	Part number	Package
	PM2.5WNCA	50
	PM2.5WNCB	50
	TM42W	10
0.4 x 2.5 DNT11-0102		



PMM2.5WN-XXP			
Rated Data		UL	IEC
Rated Voltage	(V)	600	800
Rated Current	(A)	20	24
Rated impulse voltage		8KV	
Wire range	(AWG/mm²)	28–12	0.5–2.5
Connection Capacity			
Max. Solid	(mm²)	4	
Max. Stranded	(mm²)	2.5	
General Data			
Torque	(N.m)		
Screws			
Stripping length	(mm)	8–10	
Insulation material		PA	
T x H x W	(mm)	10 x 22 x 32	
Package		50	
Color	Part number	Packag	
	PMM2.5WN-02P...12P-RD	50	
	PMM2.5WN-02P...12P-BL	50	
	PMM2.5WN-02P...12P-YG	50	
Part number		Package	
PMM2.5WNCA		50	
PMM2.5WNCB		50	
TM42W		10	
0.4 x 2.5 DNT11-0102			





PM2.5WNH1-XXP		
Mounting hole diameter: Ø3.2x4.6mm		
Mounting hole diameter: Ø3.2x4.6mm		
PMM2.5WNH1-XXP		



Assembled blocks	End cover	Single block	End cover with spring clamp
PM2.5WN-XXP	PM2.5WNCA	PM2.5WN	PM2.5WNCB
PMM2.5WN-XXP	PMM2.5WNCA	PMM2.5WN	PMM2.5WNCB


PM..N-XXP




PM2.5N-XXP			
Rated Data		UL	IEC
Rated Voltage	(V)	300	500
Rated Current	(A)	20	24
Rated impulse voltage		6KV	
Wire range (AWG/mm ²)		22~12	0.34~2.5
Connection Capacity			
Max. Solid	(mm ²)	4	
Max. Stranded	(mm ²)	2.5	
General Data			
Torque (N.m)		0.39	
Screws		M2.5	
Stripping length (mm)		6~8	
Insulation material		PA	
T x H x W (mm)		5.1 x 20 x 22	
Package		50	

Color	Part number	Package
■	PM2.5N-01P...12P-OR	50
■	PM2.5NG-01P...12P	50

Part number	Package
PM2.5NC	50
CSC-2.502PS	2~4P/50
CSC-2.505PS	5~10P/10
TM42W	10
TM-R100	10
PMH	50
#0/3.0 DNT11-0201	





Assembled blocks	End cover	Single block	End cover with spring clamp
PM2.5N-XXP	PM2.5NC	PM2.5N	-
PM4N-XXP	PM4NC	PM4N	-
PM6N-XXP	PM6NC	PM6N	-



PM4N-XXP			
Rated Data		UL	IEC
Rated Voltage	(V)	300	500
Rated Current	(A)	30	32
Rated impulse voltage		6KV	
Wire range (AWG/mm ²)		22~10	0.5~4
Connection Capacity			
Max. Solid	(mm ²)	6	
Max. Stranded	(mm ²)	4	
General Data			
Torque (N.m)		0.49	
Screws		M3	
Stripping length (mm)		6~8	
Insulation material		PA	
T x H x W (mm)		6.1 x 23 x 22	
Package		50	

Color	Part number	Package
■	PM4N-01P...12P-OR	50
■	PM4NG-01P...12P	50


Part number	Package
PM4NC	50
CSC-402PS	2-4P/50
CSC-410PS	5-10P/10
TM43W	10
TM-R100	10
PMH	50
#0/3.0 DNT11-0201	




PM6N-XXP			
Rated Data		UL	IEC
Rated Voltage	(V)	300	500
Rated Current	(A)	65	41
Rated impulse voltage		6KV	
Wire range	(AWG/mm ²)	20~6	0.5~6
Connection Capacity			
Max. Solid	(mm ²)	10	
Max. Stranded	(mm ²)	6	
General Data			
Torque		(N.m)	
Screws		M4	
Stripping length		(mm)	
Insulation material		PA	
T x H x W		(mm)	
Package		50	

Color	Part number	Package
■	PM6N-01P...07P-OR	50
	PM6N-08P...12P-OR	20
■	PM6NG-01P...07P	50

Part number	Package
PM6NC	50
CSC-602PS	2~4P/50
CSC-610PS	5~10P/10
TM49W	10
TM-R200	10
PMH	50
#0/3.0 DNT11-0201	




A diagram showing a bolted joint. A bolt is inserted through a plate, secured with a lock washer and a lock nut. The lock washer is a thin, circular disc with a serrated edge that fits between the bolt head and the lock nut. The lock nut is a nut with a serrated edge that fits onto the bolt. The lock washer and lock nut are used to prevent the bolt from loosening due to vibration or movement.



PM6H-XXP			
Rated Data		UL	IEC
Rated Voltage	(V)	300	800
Rated Current	(A)	50	57
Rated impulse voltage			8KV
Wire range (AWG/mm ²)		20-8	0.5-10
Connection Capacity			
Max. Solid	(mm ²)		10
Max. Stranded	(mm ²)		10
General Data			
Torque	(N.m)	0.9-1.2	
Screws		M4	
Stripping length		(mm) 9-10	
Insulation material		PA	
T x H x W	(mm)	13.5 x 25.5 x 25.6	
Package		50	


Color	Part number	Package



PM10-XXP			
Rated Data		UL	IEC
Rated Voltage	(V)	300	400
Rated Current	(A)	45	57
Rated impulse voltage			6KV
Wire range (AWG/mm ²)		22~8	0.5~10
Connection Capacity			
Max. Solid	(mm ²)		10
Max. Stranded	(mm ²)		10
General Data			
Torque (N.m)		1.75	
Screws		M4	
Stripping length (mm)		12~13	
Insulation material		PA	
T x H x W (mm)		8.2 x 31 x 30	
Package		50	


Color	Part number	Packag
■	PM10-01P...07P-OR	50
	PM10-08P...12P-OR	20

Part number	Package
PM10C	50
TM44W	10
TM-R100	10
1.0x5.5 DNT11-0111	



PM16H-XXP			
Rated Data		UL	IEC
Rated Voltage	(V)	600	1000
Rated Current	(A)	100	76
Rated impulse voltage			6KV
Wire range (AWG/mm ²)		14~3	1.5~16
Connection Capacity			
Max. Solid	(mm ²)		16
Max. Stranded	(mm ²)		16
General Data			
Torque (N.m)		2~2.5	
Screws		M5	
Stripping length (mm)		14~16	
Insulation material		PA	
T x H x W (mm)		16.5 x 30 x 36.9	
Package		50	

Color	Part number	Package



Rated Data		UL	IEC
Rated Voltage	(V)		
Rated Current	(A)		
Rated impulse voltage			
Wire range	(AWG/mm ²)		
Connection Capacity			
Max. Solid	(mm ²)		
Max. Stranded	(mm ²)		
General Data			
Torque	(N.m)		
Screws			
Stripping length	(mm)		
Insulation material			
T x H x W	(mm)		
Package			

Color	Part number	Package






Part number	Package

Accessories








- DIN rail terminal blocks offer full range of accessories, including covers, end brackets, partition plates, bridges, fuse, hand tools and marking system.
- Marking block helps to save space directly on terminal block.
- Cross connection system provides plug-in and side insertion bridges.






End Bracket

SS2N	SS3	SS4N	SS5N
			
			

Part number	DIN Rail	Marking label	Package
SS2N	TS-35, TS-35/15	TM43W, TM48W, TM-R100, TM-R200	50
SS3	TS-35, TS-35/15	-	50
SS4N	TS-35, TS-35/15	TM49W, TM-R200	50
SS5N	TS-35, TS-35/15	TM49W, TM-R200	50





SS6N	SS7N	SS11	SS13
			
			






Part number	DIN Rail	Bus size	Marking label	Package
SS6N	TS-35, TS-35/15	3x10, 6x6	TM50W, TM-R200	50
SS7N	TS-35, TS-35/15	3x10, 6x6	TM44W, TM49W, TM-R100, TM-R200	50
SS11	TS-35, TS-35/15	-	TM49W	50
SS13	TS-35, TS-35/15	-	TM49W, TM-R200	50

SS9A	SS9B	SS9C	
			
			





Part number	Compatible Product	Package
SS9A	TS-35, TS-35/15	50
SS9B	TS-35, TS-35/15	50
SS9C	TS-35, TS-35/15	50

Marking Block





MKG-001	MKG-002	MKG-003	MKG-004
			
			
Part number	Compatible Product	Marking label	Package
MKG-001	SS2N, SS6N, SS7N, DP Series, AK Series	TM46W / TM-R200	200
MKG-002	SS2N, SS6N, SS7N, DP Series, AK Series	TM46W / TM-R200	200
MKG-003	SS2N, SS6N, SS7N, DP Series, AK Series	TM46W / TM-R200	200
MKG-004	SS2N, SS6N, SS7N, DP Series, AK Series	TM46W / TM-R200	200





MKH-001	MKH-002	MKW	MKL	MKL-001
				
				
Part number	Compatible Product	Marking label	Package	
MKH-001	DP2.5SGC, SS4N, SS5N, SS7N, SS11	TM-R100	50	
MKH-002	SS6N	TM-R200	50	
MKW	TS-35, TS-35/15		20	
MKL	SS4N, SS5N	TM-R100	100	
MKL-001	SS13	TM-R110	100	


Separating Disk

DKNSPS-001	DKNSPS-002	DKNSPS-003	DKNSPS-004
			
			
Part number	Compatible Product	Package	
DKNSPS-001	DK2.5N, DK4N, DK2.5N-TN, DK4N-TN, DK2.5N-TR, DK4N-TR, DKK2.5N Series, DKK4N Series	50	
DKNSPS-002	DK6N, DK10N, DK6N-TN, DK10N-TN	50	
DKNSPS-003	DK16H	50	
DKNSPS-004	DK16N,DK35N, DK35H	50	








Partition Plate











AKSPS-001	AKSPS-002	AKSPS-003	AKSPS-004
			
			
Part number	Compatible Product	Package	
AKSPS-001	DP1.5N, DP2.5N, DP4N, DP1.5N-PE, DP2.5N-PE, DP4N-PE, AK1.5, AK2.5, AK4	50	
AKSPS-002	DP6N, DP6N-PE, AK6	50	
AKSPS-003	DP1.5N-TN, DP2.5N-TN, DP4N-TN, DP6N-TN, DP1.5N-TN-PE, DP2.5N-TN-PE, DP4N-TN-PE, DP6N-TN-PE, AK1.5-TN, AK2.5-TN, AK4-TN, AK2.5-TP, AK4-TP, AK2.5-TG, AK4-TG, AK2.5-CP, AK4-CP, AK4-TF(5X20), AK4-TFLXX(5X20)	50	
AKSPS-004	DP1.5N-TR, DP2.5N-TR, DP1.5N-TR-PE, DP2.5N-TR-PE, AK1.5-TR, AK2.5-TR, AK2.5-TN-TP, AK2.5-TN-TG, AK2.5-TN-CP	50	

AKSPS-005	DKNSPS-005	DKNSPS-008	DKNSPS-009
			
			
Part number	Compatible Product	Package	
AKSPS-005	DP4N-TR, DP4N-TR-PE, AK4-TR	50	
DKNSPS-005	DK2.5N, DK4N	50	
DKNSPS-008	DK2.5N, DK4N, DK6N	50	
DKNSPS-009	DK10N, DK16N	50	

DKNSPS-010		
		
		
Part number	Compatible Product	Package
DKNSPS-010	DK35N	50



Reducing Bridge

							
Part number	Compatible Products						Package
DSD02-2.5/6	DK2.5N, DK6N, DK2.5N-TN, DK6N-TN, DK2.5N-TR						100
DSD02-2.5/10	DK2.5N, DK10N, DK2.5N-TN, DK10N-TN, DK2.5N-TR						100
DSD02-2.5/16	DK2.5N, DK16N, DK2.5N-TN, DK2.5N-TR						100
DSD02-4/6	DK4N, DK6N, DK4N-TN, DK6N-TN, DK4N-TR						100
DSD02-4/10	DK4N, DK10N, DK4N-TN, DK10N-TN, DK4N-TR						100
DSD02-4/16	DK4N-DK16N, DK4N-TN, DK4N-TR						100
DSD02-6/16	DK6N, DK16N, DK6N-TN						100




										
---	---	---	---	---	---	---	--	---	---	---

Part number	Compatible Products	Package
DSD03-1.5/2.5	DP1.5N, DP2.5N, DP1.5N-TN, DP2.5N-TN, DP1.5N-TR, DP2.5N-TR, DPD10-P001, DPD16-P001	100
DSD03-1.5/4	DP1.5N, DP4N, DP1.5N-TN, DP4N-TN, DP1.5N-TR, DP4N-TR	100
DSD03-2.5/4	DP2.5N, DP4N, DP2.5N-TN, DP4N-TN, DP2.5N-TR, DP4N-TR, DPD10-P001, DPD16-P001	100
DSD03-2.5/6	DP2.5N, DP6N, DP2.5N-TN, DP6N-TN, DP2.5N-TR, DP6N-TR, DKD35-P001, DKD35-P002, DPD10-P001, DPD16-P001	100
DSD03-2.5/10	DP2.5N, DP10, DP2.5N-TN, DP10-TN, DP2.5N-TR, DKD35-P003, DPD10-P001, DPD16-P001	100
DSD03-2.5/16	DP2.5N, DP16, DP2.5N-TN, DP2.5N-TR, DPD10-P001, DPD16-P001	100
DSD03-4/6	DP4N, DP6N, DP4N-TN, DP6N-TN, DP4N-TR, DP6N-TR, DKD35-P001	100
DSD03-4/10	DP4N, DP10, DP4N-TN, DP10-TN, DP4N-TR, DKD35-P003	100
DSD03-4/16	DP4N, DP16, DP4N-TN, DP4N-TR	100
DSD03-6/16	DP6N, DP16, DN6N-TN, DP6N-TR, DKD35-P001, DKD35-P002	100

	Conversion bridge comparison table					Specifiation	
	A (Input)	B (Output)	C (Shift cover)	D (Shift cover)	E (Reducing Bridge)	Powered by one-side	Powered by central
DK.N Series	DK6N	DK2.5N	DK6NCA	DK4NCA	DSD02-2.5/6	40A	56A
		DK4N	DK6NCA	DK4NCA	DSD02-4/6	45A	56A
	DK10N	DK2.5N	DK10NCA	DK4NCA	DSD02-2.5/10	40A	65A
		DK4N	DK10NCA	DK4NCA	DSD02-4/10	45A	65A
	DK16N	DK2.5N	DK16NCA	/	DSD02-2.5/16	40A	80A
		DK4N		/	DSD02-4/16	45A	90A
DP Series	DP2.5N	DP1.5N		/	DSD03-1.5/2.5	24A	30A
		DP1.5N		/	DSD03-1.5/4	24A	40A
	DP4N	DP2.5N		/	DSD03-2.5/4	40A	40A
		DP2.5N	DP6CA	DP2.5CA	DSD03-2.5/6	40A	56A
	DP6N	DP4N	DP6CA	DP4CA	DSD03-4/6	45A	56A
		DP2.5N	DP10CA	DP2.5CA	DSD03-2.5/10	40A	65A
	DP10	DP4N	DP10CA	DP4CA	DSD03-4/10	45A	65A
		DP2.5N	DP16CA	DP2.5CA	DSD03-2.5/16	40A	80A
		DP4N	DP16CA	DP4CA	DSD03-4/16	45A	90A
		DP6N	DP16CA	DP6CA	DSD03-6/16	37A	74A









Screw-on bridge






			
---	---	---	---

Part number	Position	Compatible Products	Package
DS2.5-XXP	02~10	DKES1.5, DKES1.5-XXP, DKES1.5M-XXP	2~4P : 100 / 5~10P : 50
DS16-XXP	02~10	DK16H, DK10-TF(5X20), DK10-TFA(5X20)	50
DS35-XXP	02~10	DK35H	50

Cross Connection System




							
---	---	---	---	---	---	---	---

Part number	Position	Compatible Products	Package
DSD01-1.5XXN	02~05,10	AK1.5, AK1.5-TN, AK1.5-TR, AKK1.5	2~4P : 100 / 5P, 10P : 50
DSD01-2.5XXN	02~10	DP2.5N, DP2.5N-TN, DP2.5N-TR, DP2.5N-PE, DP2.5N-TN-PE, DP2.5N-TR-PE, DPP2.5N Series, DP2.5N-3L Series, DPD16-P001, DPD10-P001, DP2.5SG Series, DPES2.5, DPES2.5-PE, DP2.5N-TP, DP2.5N-TG, DP2.5N-CP, DPP2.5N-TP, DPP2.5N-TG, DPP2.5N-CP, AK2.5, AK2.5-TN, AK2.5-TR, AK2.5-TP, AK2.5-TN-TP, AK2.5-TR-TP, AK2.5-TG, AK2.5-TN-TG, AK2.5-TR-TG, AK2.5-CP, AK2.5-TN-CP, AK2.5-TR-CP, AKK2.5, AKK2.5-D01, AKK2.5-D02, AKK2.5-D03, AKK2.5-D04, AKK2.5-PV	2~4P : 100 / 5~10P : 50
DSD01-4XXN	02~05,10	DP4N, DP4N-TN, DP4N-TR, DP4N-PE, DP4N-TN-PE, DP4N-TR-PE, DPP4N Series, DP4N-TP, DP4N-TG, DP4N-CP, DP4N-TF(5X20), DP4N-TFLXX(5X20), DP4N-TFU, DP4N-TFUL, DP4N-TFU(5X20), DP4N-TFUL(5X20), AK4, AK4-TN, AK4-TR, AKK4, AK4-TP, AK4-TG, AK4-CP, AK4-TF(5X20), AK4-TFLXX(5X20)	2~4P : 100 / 5P, 10P : 50
DSD01-6XXN	02~05,10	DP6N, DP6N-TN, DP6N-TR, DP6N-PE, DP6N-TN-PE, DP6N-TR-PE, DPTD6N, DPTL6N, DPTD6N-D05, DPTD6N-D06, DKD35-P001, DKD35-P002, DP6N-TF-6.3X32, DP6N-TFL-6.3X32, AK6, AK6-TN, AK6-TR	2~4P : 100 / 5P, 10P : 50
DSD01-10XXN	02~05	DP10, DP10-PE, DP10-TN-PE, AK10, AK10-TN, DKD35-P003	50
DSD01-16XXN	02	DP16, AK16, AK16-TN	50
DSD01-3502N	02	AK35	50






						
---	---	---	---	---	---	---




Part number	Position	Compatible Products	Package
DSD03-1.5XX	02~10, 20	DP1.5N, DP1.5N-TN, DP1.5N-TR, DP1.5N-PE, DP1.5N-TN-PE, DP1.5N-TR-PE, DPP1.5N Series, DPD10-P001, DKD35-P002	100
DSS2.5N-XXP	02~10, 20	DK2.5N, DK2.5N-TN, DK2.5N-TR, DKK2.5N, DKK2.5N-PV, DKK2.5N-L2PE, DKK2.5N-PE, DKK2.5N-TP, DKK2.5N-TG, DKK2.5N-CP	2~4P : 100 / 5~10P, 20P : 50
DSS4N-XXP	02~10	DK4N, DK4N-TN, DK4N-TR, DKK4N, DKK4N-PV, DKK4N-L2PE, DKK4N-PE, DKK4N-TP, DKK4N-TG, DKK4N-CP	2~4P : 100 / 5~10P : 50
DSS6N-XXP	02~10	DK6N, DK6N-TN	2~4P : 100 / 5~10P : 50
DSS10N-XXP	02~10	DK10N, DK10N-TN	50

Cross Connection System





	 DSS16N-02PN	 DSS35N-02PN		 DSS2.5N-6688-XXP
Part number	Position	Compatible Products		Package
DSS16N-02PN	02	DK16N		50
DSS35N-02PN	02	DK35N		50
DSS2.5N-6688-XXP	02-05	DK2.5N, DK2.5N-TN, DKK2.5N Series		2P : 100 / 3-5P : 50

Insertion bridge

	 CSC-2.5..PN	 CSC-4..PN	 CSC-6..PN	 CSC-10..PN	 CSC-16..PN
Part number	Position	Compatible Products			Package
CSC-2.5XXPN	02-10	DK2.5N, DK2.5N-TN, DK2.5N-TR, DKK2.5N Series, DK2.5N-TP, DK2.5N-TG, DK2.5N-CP			2-4P : 100 / 5-10P : 50
CSC-4XXPN	02-10	DK4N, DK4N-TN, DK4N-TR, DKK4N Series, DK4N-TP, DK4N-TG, DK4N-CP			2-4P : 100 / 5-10P : 50
CSC-6XXPN	02-10	DK6N, DK6N-TN, DK4N-TF(5X20), DK4N-TFL(5X20), DKK4N-TF(5X20), DKK4N-TFLXX(5X20)			2-4P : 100 / 5-10P : 50
CSC-10XXPN	02-10	DK10N, DK10N-TN			50
CSC-16XXPN	02, 03, 10	DK10-TF(5X20), DK10-TFA(5X20)			50




	 CSC-6..P	 CSC-16..P	 CSC-35..P	
--	---	--	---	--







Part number	Position	Compatible Products	Package
CSC-6XXP	02-10	DK6N, DKTD6N	2-4P : 100 / 5-10P : 50
CSC-16XXP	02-04, 10	DK16H, DK16N	50
CSC-35XXP	02-10	DK35H, DK35N	50

	 CSC-50..P	 CSC-95..P	 CSC-150..P	 CSC-240..P
--	--	--	--	---





Part number	Position	Compatible Products	Package
CSC-50XXP	02, 03	DK50	50
CSC-95XXP	02, 03	DK95	50
CSC-150XXP	02, 03	DK150	50
CSC-240XXP	02, 03	DK240	50





Insertion bridge

	 CSC-2.5..PS	 CSC-4..PS	 CSC-6..PS
Part number	Position	Compatible Products	Package
CSC-2.5XXPS	02-10	DK2.5S, PM2.5N-XXP	2-4P : 100 / 5-10P : 50
CSC-4XXPS	02-10	DK4S, PM4N-XXP	2-4P : 100 / 5-10P : 50
CSC-6XXPS	02-10	DK6S, PM6N-XXP	2-4P : 100 / 5-10P : 50

	 CSK11-15..-A	 CSK11-20..-A	 CSK11-30..-A	 CSK11-40..-A	 CSK11-60..-A
Part number	Position	Compatible Products	Package		
CSK11-15XX-A	02, 03, 06, 20	DKU15, DKUP15-XXPK, DKB15N, DKB15N-XXPCK	2P, 3P : 100 / 6P, 10P, 20P : 50		
CSK11-20XX-A	02, 03, 06, 20	DKU20, DKUP20-XXPK, DKB20N, DKB20N-XXPCK	2P, 3P : 100 / 6P, 10P, 20P : 50		
CSK11-30XX-A	02, 03, 06, 10	DKU30, DKUP30-XXPK, DKB30N, DKB30N-XXPCK	2P, 3P : 100 / 6P, 10P : 50		
CSK11-40XX-A	02, 03	DKU40, DKUP40-XXPK, DKB40N, DKB40N-XXPCK	2P, 3P :100		
CSK11-60XX-A	02, 03	DKU60, DKUP60-XXPK, DKB60N, DKB60N-XXPCK	2P, 3P :100		


Part number	Position	Compatible Products	Package
CSK11-15XX-A	02, 03, 06, 20	DKU15, DKUP15-XXPK, DKB15N, DKB15N-XXPCK	2P, 3P : 100 / 6P, 10P, 20P : 50
CSK11-20XX-A	02, 03, 06, 20	DKU20, DKUP20-XXPK, DKB20N, DKB20N-XXPCK	2P, 3P : 100 / 6P, 10P, 20P : 50
CSK11-30XX-A	02, 03, 06, 10	DKU30, DKUP30-XXPK, DKB30N, DKB30N-XXPCK	2P, 3P : 100 / 6P, 10P : 50
CSK11-40XX-A	02, 03	DKU40, DKUP40-XXPK, DKB40N, DKB40N-XXPCK	2P, 3P :100
CSK11-60XX-A	02, 03	DKU60, DKUP60-XXPK, DKB60N, DKB60N-XXPCK	2P, 3P :100

	 CSK01-10..-A		 CSK01-10..-B
---	---	---	---

	 CSK02-10..-A		 CSK02-10..-B
---	---	---	---


Part number	Position	Compatible Products	Package
CSK01-10XX-A	02-10	DKBB10, DKBB10-XXPCK	50
CSK01-10XX-B	02-10	DKBB10, DKBB10-XXPCK	50
CSK02-10XX-A	02-10	DKBB10, DKBB10-XXPCK	50
CSK02-10XX-B	02-10	DKBB10, DKBB10-XXPCK	50
CSK01-60XX-A	02-10	DKB80, DKB80-XXPCK	50
CSK01-60XX-B	02-10	DKB80, DKB80-XXPCK	50
CSK02-60XX-A	02-10	DKB80, DKB80-XXPCK	50
CSK02-60XX-B	02-10	DKB80, DKB80-XXPCK	50

FUSE




Part number	Compatible Products	Package
FUK1A-01	DP4N-TF(5X20), DP4N-TFLXX(5X20), DP4N-TFH(5X20), DP4N-TFHLXX(5X20), DP4N-TFU(5X20), DP4N-TFULXX(5X20), AK4-TFLXX(5X20), AK4-TF(5X20), DK4N-TF(5X20), DK4N-TFLXX(5X20), DKK4N-TF(5X20), DKK4N-TFLXX(5X20), DK10-TF(5X20), DK10-TFA(5X20)	50
FUK1A-02	DP6N-TF-6.3X32, DP6N-TFLXX-6.3X32	50
FUK2A-01	DP4N-TF(5X20), DP4N-TFLXX(5X20), DP4N-TFH(5X20), DP4N-TFHLXX(5X20), DP4N-TFU(5X20), DP4N-TFULXX(5X20), AK4-TFLXX(5X20), AK4-TF(5X20), DK4N-TF(5X20), DK4N-TFLXX(5X20), DKK4N-TF(5X20), DKK4N-TFLXX(5X20), DK10-TF(5X20), DK10-TFA(5X20)	50
FUK2A-02	DP6N-TF-6.3X32, DP6N-TFLXX-6.3X32	50
FUK6.3A-01	DP4N-TF(5X20), DP4N-TFLXX(5X20), DP4N-TFH(5X20), DP4N-TFHLXX(5X20), DP4N-TFU(5X20), DP4N-TFULXX(5X20), AK4-TFLXX(5X20), AK4-TF(5X20), DK4N-TF(5X20), DK4N-TFLXX(5X20), DKK4N-TF(5X20), DK10-TF(5X20), DK10-TFA(5X20)	50
FUK6.3A-02	DP6N-TF-6.3X32, DP6N-TFLXX-6.3X32	50

DIN Rail Cap




Part number	Compatible Products	Package
PMH	PM2.5N, PM4N, PM6N	50
TS-35C	TS-35	1000

DIN Rail & DIN Rail Cutter



* Specific length of rail available upon request.

Part number	Compatible Product	Package
TS-15	DK...S Series	20
TS-35	DP...Series, DK...N Series, DK...Series, AK...Series, DKB...Series, DKU...Series, DKM...Series	20
TS-35/15	DP...Series, DK...N Series, AK...N Series, DKB...Series, DKU...Series, DKM...Series	10



Part number	DIN Rail	Package
TSC-S01	TS-35	1
TSC-S02	TS-35, TS-35/15	1